

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259868

Luminaire Tested: P3AS13R129050DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259868
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R129050DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 5000K CCT AND, 90CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 725.0 lumens
Efficiency: N/A
Efficacy: 46.8 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 15.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259868

CATALOG NUMBER: P3AS13R129050DE010 E3PHLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1259868

CATALOG NUMBER: P3AS13R129050DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95
2	104	98	93	89	102	97	92	88	93	89	86		90	87	84		87
3	98	90	84	79	96	88	83	78	85	81	77		83	79	75		81
4	92	82	76	70	90	81	75	70	79	73	69		77	72	68		75
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70
6	81	71	63	58	79	70	63	58	68	62	58		67	61	57		65
7	77	66	59	54	75	65	58	54	64	58	53		62	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	69	58	51	47	68	57	51	46	56	50	46		55	50	46		54
10	65	54	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	210970
5°	197776
10°	162188
15°	125994
20°	99455
25°	79263
30°	63630
35°	51932
40°	42794
45°	36004
50°	30907
55°	26761
60°	23726
65°	20651
70°	18336
75°	14827
80°	11996
85°	8051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 36004 cd/sqm

TEST NUMBER: P1259868

CATALOG NUMBER: P3AS13R129050DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.3	11.1
10°-20°	155.5	21.4
20°-30°	151.1	20.8
30°-40°	122.1	16.8
40°-50°	90.7	12.5
50°-60°	63.4	8.7
60°-70°	39.7	5.5
70°-80°	18.8	2.6
80°-90°	3.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	386.8	53.4
0°-40°	509.0	70.2
0°-60°	663.0	91.4
0°-90°	725.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	725.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	962	
5°	898	80
15°	555	155
25°	328	151
35°	194	122
45°	116	91
55°	70	63
65°	40	40
75°	18	19
85°	3	3
90°	0	

TEST NUMBER: P1259868

CATALOG NUMBER: P3AS13R129050DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	962.1
2.5°	946.2
5°	898.5
7.5°	822.2
10°	728.4
12.5°	636.1
15°	555.0
17.5°	486.6
20°	426.2
22.5°	373.7
25°	327.6
27.5°	286.3
30°	251.3
32.5°	221.1
35°	194.0
37.5°	170.2
40°	149.5
42.5°	132.0
45°	116.1
47.5°	103.4
50°	90.6
52.5°	79.5
55°	70.0
57.5°	62.0
60°	54.1
62.5°	46.1
65°	39.8
67.5°	33.4
70°	28.6
72.5°	22.3
75°	17.5
77.5°	12.7
80°	9.5
82.5°	4.8
85°	3.2
87.5°	0.0
90°	0.0

(END OF REPORT)