

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259869

Luminaire Tested: P3AS13R129050DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259869
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R129050DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 5000K CCT AND, 90CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 513.0 lumens
Efficiency: N/A
Efficacy: 33.1 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 15.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259869

CATALOG NUMBER: P3AS13R129050DE010 E3PHLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1259869

CATALOG NUMBER: P3AS13R129050DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		95
2	105	99	94	90	102	97	92	89	94	90	87		91	87	85		88
3	99	91	85	80	96	89	84	80	87	82	78		84	80	77		82
4	93	84	78	73	91	83	77	72	81	76	71		79	74	71		77
5	88	78	72	67	86	77	71	67	76	70	66		74	69	65		72
6	83	73	67	62	82	73	66	62	71	65	61		70	65	61		68
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	59	52	48	68	58	52	48	57	52	48		56	51	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	192002
5°	176293
10°	140478
15°	104972
20°	79737
25°	60366
30°	44665
35°	31909
40°	21841
45°	15288
50°	12997
55°	12769
60°	13245
65°	14009
70°	14233
75°	14827
80°	16037
85°	16102

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 18648 cd/sqm

TEST NUMBER: P1259869

CATALOG NUMBER: P3AS13R129050DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.9	13.8
10°-20°	129.7	25.3
20°-30°	114.9	22.4
30°-40°	75.3	14.7
40°-50°	40.2	7.8
50°-60°	30.4	5.9
60°-70°	26.2	5.1
70°-80°	18.0	3.5
80°-90°	7.4	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	315.6	61.5
0°-40°	390.8	76.2
0°-60°	461.5	90.0
0°-90°	513.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	513.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	876	
5°	801	71
15°	462	130
25°	250	115
35°	119	75
45°	49	40
55°	33	30
65°	27	26
75°	18	18
85°	6	7
90°	0	

TEST NUMBER: P1259869

CATALOG NUMBER: P3AS13R129050DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	875.6
2.5°	855.0
5°	800.9
7.5°	721.5
10°	630.9
12.5°	543.5
15°	462.4
17.5°	397.3
20°	341.7
22.5°	292.4
25°	249.5
27.5°	211.4
30°	176.4
32.5°	146.2
35°	119.2
37.5°	95.3
40°	76.3
42.5°	60.4
45°	49.3
47.5°	42.9
50°	38.1
52.5°	36.6
55°	33.4
57.5°	31.8
60°	30.2
62.5°	28.6
65°	27.0
67.5°	23.8
70°	22.2
72.5°	19.1
75°	17.5
77.5°	14.3
80°	12.7
82.5°	11.1
85°	6.4
87.5°	3.2
90°	0.0

(END OF REPORT)