

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259912

Luminaire Tested: P3AS13R209050DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259912
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R209050DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R20 optic, 5000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1331.0 lumens
Efficiency: N/A
Efficacy: 91.2 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259912

CATALOG NUMBER: P3AS13R209050DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1259912

CATALOG NUMBER: P3AS13R209050DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	114	112	110	113	111	110	108	107	106	105		104	103	102		100
2	112	109	106	104	110	107	105	103	104	102	101		101	100	98		99
3	109	105	102	99	107	104	101	98	101	99	97		99	97	95		97
4	106	101	98	95	105	100	97	95	99	96	94		97	95	93		95
5	104	98	95	92	102	98	94	92	96	93	91		95	92	90		93
6	101	96	92	89	100	95	92	89	94	91	89		93	90	88		92
7	99	93	90	87	98	93	89	87	92	89	86		91	88	86		90
8	97	91	87	85	96	91	87	85	90	87	85		89	86	84		88
9	95	89	85	83	94	89	85	83	88	85	83		87	84	83		87
10	93	87	84	81	92	87	83	81	86	83	81		86	83	81		85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2019027
5°	1699930
10°	1061748
15°	396938
20°	136255
25°	56786
30°	26738
35°	11993
40°	5668
45°	2915
50°	1058
55°	191
60°	219
65°	259
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2915 cd/sqm

TEST NUMBER: P1259912

CATALOG NUMBER: P3AS13R209050DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	642.2	48.3
10°-20°	529.0	39.7
20°-30°	120.2	9.0
30°-40°	30.6	2.3
40°-50°	7.7	0.6
50°-60°	1.0	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1291.4	97.0
0°-40°	1322.0	99.3
0°-60°	1330.7	100.0
0°-90°	1331.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1331.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9208	
5°	7723	642
15°	1748	529
25°	235	120
35°	45	31
45°	9	8
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1259912

CATALOG NUMBER: P3AS13R209050DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	9207.5
1°	9129.4
2°	8899.4
3°	8569.5
4°	8164.6
5°	7722.8
6°	7230.5
7°	6687.2
8°	6053.3
9°	5425.2
10°	4768.4
11°	4069.5
12°	3371.7
13°	2780.5
14°	2215.3
15°	1748.5
16°	1380.1
17°	1088.7
18°	874.8
19°	711.4
20°	583.9
21°	488.1
22°	407.5
23°	338.8
24°	282.6
25°	234.7
27.5°	153.5
30°	105.6
32.5°	65.1
35°	44.8
37.5°	28.6
40°	19.8
42.5°	13.5
45°	9.4
47.5°	6.2
50°	3.1
52.5°	1.6
55°	0.5
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P1259912

CATALOG NUMBER: P3AS13R209050DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)