

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260493

Luminaire Tested: P3AS17R559050DE010 E3DL1MW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1260493  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R559050DE010 E3DL1MW  
Description: 3in Adjustable LED luminaire with, R55 optic, 5000K CCT AND, 90CRI , E3DL1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1533.0 lumens  
Efficiency: N/A  
Efficacy: 72.3 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1260493

CATALOG NUMBER: P3AS17R559050DE010 E3DL1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1260493

CATALOG NUMBER: P3AS17R559050DE010 E3DL1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 111 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 103 | 101 |  | 101 | 99  | 98  |  | 97  |
| 2   | 108 | 103 | 99  | 95  | 106 | 101 | 97  | 94  | 98  | 95  | 92  |  | 95  | 92  | 90  |  | 92  |
| 3   | 102 | 96  | 91  | 87  | 100 | 94  | 90  | 86  | 92  | 88  | 85  |  | 89  | 86  | 83  |  | 87  |
| 4   | 97  | 90  | 84  | 80  | 95  | 89  | 83  | 79  | 86  | 82  | 78  |  | 84  | 81  | 78  |  | 82  |
| 5   | 92  | 84  | 78  | 74  | 91  | 83  | 78  | 74  | 81  | 77  | 73  |  | 80  | 76  | 72  |  | 78  |
| 6   | 88  | 79  | 73  | 69  | 86  | 78  | 73  | 68  | 77  | 72  | 68  |  | 75  | 71  | 68  |  | 74  |
| 7   | 84  | 74  | 68  | 64  | 82  | 74  | 68  | 64  | 72  | 67  | 64  |  | 71  | 67  | 63  |  | 70  |
| 8   | 80  | 70  | 64  | 60  | 78  | 70  | 64  | 60  | 69  | 63  | 60  |  | 67  | 63  | 60  |  | 67  |
| 9   | 76  | 66  | 61  | 57  | 75  | 66  | 60  | 56  | 65  | 60  | 56  |  | 64  | 59  | 56  |  | 63  |
| 10  | 73  | 63  | 57  | 53  | 72  | 62  | 57  | 53  | 62  | 57  | 53  |  | 61  | 56  | 53  |  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 420953 |
| 5°  | 416684 |
| 10° | 402397 |
| 15° | 371943 |
| 20° | 320955 |
| 25° | 253490 |
| 30° | 179825 |
| 35° | 115964 |
| 40° | 69645  |
| 45° | 39260  |
| 50° | 21117  |
| 55° | 7531   |
| 60° | 6798   |
| 65° | 6590   |
| 70° | 6283   |
| 75° | 5931   |
| 80° | 5304   |
| 85° | 3522   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 39260 cd/sqm

TEST NUMBER: P1260493

CATALOG NUMBER: P3AS17R559050DE010 E3DL1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 178.0  | 11.6      |
| 10°-20°   | 453.1  | 29.6      |
| 20°-30°   | 474.8  | 31.0      |
| 30°-40°   | 277.0  | 18.1      |
| 40°-50°   | 103.7  | 6.8       |
| 50°-60°   | 24.4   | 1.6       |
| 60°-70°   | 12.6   | 0.8       |
| 70°-80°   | 7.4    | 0.5       |
| 80°-90°   | 2.1    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 1105.9 | 72.1      |
| 0°-40°    | 1382.9 | 90.2      |
| 0°-60°    | 1511.0 | 98.6      |
| 0°-90°    | 1533.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1533.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1920 |      |
| 5°  | 1893 | 178  |
| 15° | 1638 | 453  |
| 25° | 1048 | 475  |
| 35° | 433  | 277  |
| 45° | 127  | 104  |
| 55° | 20   | 24   |
| 65° | 13   | 13   |
| 75° | 7    | 7    |
| 85° | 1    | 2    |
| 90° | 0    |      |

TEST NUMBER: P1260493

CATALOG NUMBER: P3AS17R559050DE010 E3DL1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1919.7 |
| 2.5°  | 1914.1 |
| 5°    | 1893.0 |
| 7.5°  | 1859.2 |
| 10°   | 1807.2 |
| 12.5° | 1734.0 |
| 15°   | 1638.4 |
| 17.5° | 1517.5 |
| 20°   | 1375.4 |
| 22.5° | 1216.5 |
| 25°   | 1047.7 |
| 27.5° | 874.8  |
| 30°   | 710.2  |
| 32.5° | 561.1  |
| 35°   | 433.2  |
| 37.5° | 329.1  |
| 40°   | 243.3  |
| 42.5° | 174.4  |
| 45°   | 126.6  |
| 47.5° | 91.4   |
| 50°   | 61.9   |
| 52.5° | 35.2   |
| 55°   | 19.7   |
| 57.5° | 16.9   |
| 60°   | 15.5   |
| 62.5° | 14.1   |
| 65°   | 12.7   |
| 67.5° | 11.3   |
| 70°   | 9.8    |
| 72.5° | 8.4    |
| 75°   | 7.0    |
| 77.5° | 5.6    |
| 80°   | 4.2    |
| 82.5° | 2.8    |
| 85°   | 1.4    |
| 87.5° | 1.4    |
| 90°   | 0.0    |

(END OF REPORT)