

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259918

Luminaire Tested: P3AS13R209050DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259918
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R209050DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 5000K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 410.0 lumens
Efficiency: N/A
Efficacy: 28.1 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259918
CATALOG NUMBER: P3AS13R209050DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1259918
 CATALOG NUMBER: P3AS13R209050DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83			83
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76			76
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70			70
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65			65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60			60
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55			55
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52			52
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48			48
10	68	58	51	47	67	57	51	47	56	51	47	56	51	47	55	50	47	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	101417
5°	98701
10°	90802
15°	79932
20°	68536
25°	57584
30°	46539
35°	35416
40°	25190
45°	16622
50°	10302
55°	6767
60°	6184
65°	5656
70°	5321
75°	4829
80°	4546
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16622 cd/sqm



TEST NUMBER: P1259918
 CATALOG NUMBER: P3AS13R209050DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.5	10.1
10°-20°	98.0	23.9
20°-30°	108.8	26.5
30°-40°	83.0	20.2
40°-50°	42.5	10.4
50°-60°	17.4	4.3
60°-70°	10.9	2.7
70°-80°	6.1	1.5
80°-90°	1.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	248.3	60.6
0°-40°	331.3	80.8
0°-60°	391.2	95.4
0°-90°	410.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	410.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	462	
5°	448	41
15°	352	98
25°	238	109
35°	132	83
45°	54	42
55°	18	17
65°	11	11
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1259918
CATALOG NUMBER: P3AS13R209050DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	462.5
1°	463.0
2°	460.9
3°	458.3
4°	454.2
5°	448.4
6°	441.7
7°	434.4
8°	426.5
9°	417.2
10°	407.8
12.5°	380.7
15°	352.1
17.5°	322.9
20°	293.7
22.5°	264.6
25°	238.0
27.5°	211.5
30°	183.8
32.5°	157.8
35°	132.3
37.5°	109.9
40°	88.0
42.5°	69.3
45°	53.6
47.5°	40.6
50°	30.2
52.5°	22.4
55°	17.7
57.5°	16.1
60°	14.1
62.5°	12.5
65°	10.9
67.5°	9.4
70°	8.3
72.5°	6.8
75°	5.7
77.5°	4.7
80°	3.6
82.5°	2.6
85°	1.6
87.5°	0.5
90°	0.0

(END OF REPORT)