

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260496

Luminaire Tested: P3AS17R559050DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260496
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R559050DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 5000K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 583.0 lumens
Efficiency: N/A
Efficacy: 27.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260496

CATALOG NUMBER: P3AS17R559050DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1260496

CATALOG NUMBER: P3AS17R559050DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	51	72	62	55	51	60	55	50		59	54	50		58
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	109618
5°	108210
10°	103962
15°	97231
20°	88698
25°	79142
30°	69226
35°	57500
40°	45342
45°	30763
50°	18797
55°	9749
60°	9078
65°	8561
70°	7950
75°	7032
80°	6945
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30763 cd/sqm

TEST NUMBER: P1260496

CATALOG NUMBER: P3AS17R559050DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.1	7.9
10°-20°	119.7	20.5
20°-30°	149.9	25.7
30°-40°	133.8	22.9
40°-50°	78.4	13.4
50°-60°	27.1	4.6
60°-70°	16.4	2.8
70°-80°	9.1	1.6
80°-90°	2.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	315.7	54.2
0°-40°	449.5	77.1
0°-60°	555.0	95.2
0°-90°	583.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	583.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	500	
5°	492	46
15°	428	120
25°	327	150
35°	215	134
45°	99	78
55°	26	27
65°	16	16
75°	8	9
85°	2	3
90°	0	

TEST NUMBER: P1260496

CATALOG NUMBER: P3AS17R559050DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	499.9
2.5°	497.1
5°	491.6
7.5°	480.6
10°	466.9
12.5°	449.6
15°	428.3
17.5°	405.6
20°	380.1
22.5°	353.9
25°	327.1
27.5°	300.2
30°	273.4
32.5°	244.4
35°	214.8
37.5°	185.9
40°	158.4
42.5°	128.8
45°	99.2
47.5°	75.7
50°	55.1
52.5°	35.8
55°	25.5
57.5°	22.7
60°	20.7
62.5°	18.6
65°	16.5
67.5°	14.5
70°	12.4
72.5°	10.3
75°	8.3
77.5°	6.9
80°	5.5
82.5°	3.4
85°	2.1
87.5°	1.4
90°	0.0

(END OF REPORT)