

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259925

Luminaire Tested: P3AS13R209050DE010 E3PH1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259925
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R209050DE010 E3PH1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 5000K CCT AND, 90CRI , E3PH1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 959.0 lumens
Efficiency: N/A
Efficacy: 65.7 lumens/watt
Spacing Criteria (0/90/45): 0.32 / 0.32 / 0.32
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259925

CATALOG NUMBER: P3AS13R209050DE010 E3PH1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1259925

CATALOG NUMBER: P3AS13R209050DE010 E3PH1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	111	113	112	110	109	108	107	106		104	104	103		101
2	113	110	107	105	111	108	106	104	105	104	102		102	101	100		100
3	110	107	104	101	109	105	103	101	103	101	99		101	99	98		99
4	108	104	101	98	107	103	100	98	101	98	97		99	97	95		97
5	106	101	98	96	105	100	97	95	99	96	94		97	95	94		96
6	104	99	96	93	103	98	95	93	97	94	93		96	94	92		95
7	102	97	94	92	101	96	93	91	95	93	91		95	92	90		94
8	100	95	92	90	99	95	92	90	94	91	89		93	91	89		92
9	99	94	90	88	98	93	90	88	92	90	88		92	89	88		91
10	97	92	89	87	96	92	89	87	91	88	87		91	88	87		90

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1906996
5°	1464711
10°	902366
15°	262612
20°	35050
25°	10380
30°	3114
35°	402
40°	429
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1259925

CATALOG NUMBER: P3AS13R209050DE010 E3PH1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	554.2	57.8
10°-20°	378.0	39.4
20°-30°	24.3	2.5
30°-40°	2.4	0.2
40°-50°	0.1	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	956.5	99.7
0°-40°	958.9	100.0
0°-60°	959.0	100.0
0°-90°	959.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	959.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8697	
5°	6654	554
15°	1157	378
25°	43	24
35°	2	2
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1259925

CATALOG NUMBER: P3AS13R209050DE010 E3PH1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	8696.6
2.5°	7841.6
5°	6654.2
7.5°	5338.1
10°	4052.6
12.5°	2541.9
15°	1156.8
17.5°	366.2
20°	150.2
22.5°	79.7
25°	42.9
27.5°	21.5
30°	12.3
32.5°	6.1
35°	1.5
37.5°	1.5
40°	1.5
42.5°	0.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)