

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260504

Luminaire Tested: P3AS17R559050DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260504
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R559050DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R55 optic, 5000K CCT AND, 90CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1023.0 lumens
Efficiency: N/A
Efficacy: 48.3 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260504
CATALOG NUMBER: P3AS17R559050DE010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1260504
 CATALOG NUMBER: P3AS17R559050DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92			
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	79			
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	80	77	74	73			
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67			
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59			
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55			
9	74	64	58	54	73	63	58	54	62	57	53	62	57	53	61	56	53	52			
10	70	60	55	51	69	60	54	50	59	54	50	58	54	50	58	53	50	49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	278289
5°	271318
10°	252233
15°	224610
20°	190883
25°	154049
30°	117436
35°	83520
40°	55103
45°	32686
50°	19172
55°	11813
60°	10482
65°	9495
70°	8078
75°	7117
80°	7072
85°	7045

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 32686 cd/sqm



TEST NUMBER: P1260504
 CATALOG NUMBER: P3AS17R559050DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.4	11.2
10°-20°	274.3	26.8
20°-30°	290.5	28.4
30°-40°	196.3	19.2
40°-50°	86.0	8.4
50°-60°	30.8	3.0
60°-70°	18.1	1.8
70°-80°	9.4	0.9
80°-90°	3.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	679.3	66.4
0°-40°	875.6	85.6
0°-60°	992.4	97.0
0°-90°	1023.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1023.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1269	
5°	1233	114
15°	989	274
25°	637	291
35°	312	196
45°	105	86
55°	31	31
65°	18	18
75°	8	9
85°	3	3
90°	0	



TEST NUMBER: P1260504
CATALOG NUMBER: P3AS17R559050DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1269.1
2.5°	1259.3
5°	1232.6
7.5°	1189.0
10°	1132.8
12.5°	1065.3
15°	989.4
17.5°	905.1
20°	818.0
22.5°	726.6
25°	636.7
27.5°	548.1
30°	463.8
32.5°	383.7
35°	312.0
37.5°	247.4
40°	192.5
42.5°	144.8
45°	105.4
47.5°	77.3
50°	56.2
52.5°	39.4
55°	30.9
57.5°	28.1
60°	23.9
62.5°	21.1
65°	18.3
67.5°	15.5
70°	12.6
72.5°	11.2
75°	8.4
77.5°	7.0
80°	5.6
82.5°	4.2
85°	2.8
87.5°	1.4
90°	0.0

(END OF REPORT)