

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259932

Luminaire Tested: P3AS13R259050DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259932
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259050DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R25 optic, 5000K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1351.0 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259932

CATALOG NUMBER: P3AS13R259050DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1259932

CATALOG NUMBER: P3AS13R259050DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	110	113	111	109	108	107	106	105		103	103	102		100
2	112	108	105	103	110	107	104	102	104	102	100		101	99	98		98
3	108	104	101	98	107	103	100	97	100	98	96		98	96	94		96
4	105	100	97	94	104	99	96	93	97	95	92		96	93	91		94
5	103	97	93	90	101	96	93	90	95	92	89		93	91	89		92
6	100	94	90	87	99	93	90	87	92	89	87		91	88	86		90
7	97	91	88	85	96	91	87	85	90	87	84		89	86	84		88
8	95	89	85	83	94	89	85	82	88	84	82		87	84	82		86
9	93	87	83	80	92	86	83	80	86	82	80		85	82	80		84
10	91	85	81	78	90	84	81	78	84	80	78		83	80	78		82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1444424
5°	1339662
10°	1038925
15°	520956
20°	171142
25°	68060
30°	25523
35°	7388
40°	3349
45°	1302
50°	1092
55°	803
60°	921
65°	1090
70°	705
75°	932
80°	1389
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 80°

Luminance: 1389 cd/sqm

TEST NUMBER: P1259932

CATALOG NUMBER: P3AS13R259050DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	535.3	39.6
10°-20°	638.6	47.3
20°-30°	144.0	10.7
30°-40°	23.3	1.7
40°-50°	4.2	0.3
50°-60°	2.2	0.2
60°-70°	2.0	0.1
70°-80°	1.2	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1317.9	97.6
0°-40°	1341.3	99.3
0°-60°	1347.7	99.8
0°-90°	1351.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1351.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6587	
5°	6086	535
15°	2295	639
25°	281	144
35°	28	23
45°	4	4
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1259932

CATALOG NUMBER: P3AS13R259050DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	6587.1
1°	6576.4
2°	6523.4
3°	6425.7
4°	6278.2
5°	6086.1
6°	5856.8
7°	5608.4
8°	5324.0
9°	5013.0
10°	4665.9
11°	4265.8
12°	3805.1
13°	3323.2
14°	2806.3
15°	2294.8
17.5°	1307.6
20°	733.4
22.5°	442.6
25°	281.3
27.5°	173.0
30°	100.8
32.5°	53.1
35°	27.6
37.5°	18.0
40°	11.7
42.5°	7.4
45°	4.2
47.5°	3.2
50°	3.2
52.5°	3.2
55°	2.1
57.5°	2.1
60°	2.1
62.5°	2.1
65°	2.1
67.5°	2.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	1.1
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1259932
CATALOG NUMBER: P3AS13R259050DE010 E3CD1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)