

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260513

Luminaire Tested: P3AS17R609050DE010 E3CD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260513
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609050DE010 E3CD1MW
Description: 3in Adjustable LED luminaire with, R60 optic, 5000K CCT AND, 90CRI , E3CD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1817.9 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260513
CATALOG NUMBER: P3AS17R609050DE010 E3CD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1260513

CATALOG NUMBER: P3AS17R609050DE010 E3CD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94				94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87				87
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81				81
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76				76
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71				71
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	70	68	66				66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62				62
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	63	59	58				58
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55				55
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51				51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	434132
5°	416904
10°	429251
15°	434758
20°	383890
25°	323535
30°	262395
35°	170895
40°	78490
45°	30081
50°	10064
55°	2676
60°	2456
65°	2179
70°	1795
75°	2372
80°	1768
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 30081 cd/sqm



TEST NUMBER: P1260513
 CATALOG NUMBER: P3AS17R609050DE010 E3CD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.3	10.0
10°-20°	524.4	28.8
20°-30°	611.7	33.6
30°-40°	394.7	21.7
40°-50°	88.4	4.9
50°-60°	8.8	0.5
60°-70°	4.2	0.2
70°-80°	2.4	0.1
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1318.4	72.5
0°-40°	1713.2	94.2
0°-60°	1810.4	99.6
0°-90°	1817.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1817.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1980	
5°	1894	182
15°	1915	524
25°	1337	612
35°	638	395
45°	97	88
55°	7	9
65°	4	4
75°	3	2
85°	1	1
90°	0	



TEST NUMBER: P1260513
CATALOG NUMBER: P3AS17R609050DE010 E3CD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1979.8
2.5°	1947.4
5°	1894.0
7.5°	1891.2
10°	1927.8
12.5°	1951.7
15°	1915.1
17.5°	1805.4
20°	1645.1
22.5°	1477.8
25°	1337.2
27.5°	1199.4
30°	1036.3
32.5°	845.1
35°	638.4
37.5°	435.9
40°	274.2
42.5°	164.5
45°	97.0
47.5°	56.2
50°	29.5
52.5°	9.8
55°	7.0
57.5°	5.6
60°	5.6
62.5°	4.2
65°	4.2
67.5°	4.2
70°	2.8
72.5°	2.8
75°	2.8
77.5°	1.4
80°	1.4
82.5°	1.4
85°	1.4
87.5°	0.0
90°	0.0

(END OF REPORT)