

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259948

Luminaire Tested: P3AS13R259050DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259948
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259050DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R25 optic, 5000K CCT AND, 90CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 852.0 lumens
Efficiency: N/A
Efficacy: 58.4 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259948
CATALOG NUMBER: P3AS13R259050DE010 E3DLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1259948

CATALOG NUMBER: P3AS13R259050DE010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91	91	91	91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83	83	83	83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70	70	70	70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64	64	64	64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59	59	59	59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48	48	48	48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45	45	45	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	202484
5°	197666
10°	183163
15°	163134
20°	140199
25°	119160
30°	98091
35°	76426
40°	54989
45°	34887
50°	20639
55°	14183
60°	13025
65°	12141
70°	10899
75°	9913
80°	9345
85°	8051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 34887 cd/sqm



TEST NUMBER: P1259948
 CATALOG NUMBER: P3AS13R259050DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.3	9.8
10°-20°	199.5	23.4
20°-30°	225.4	26.5
30°-40°	178.3	20.9
40°-50°	90.1	10.6
50°-60°	36.1	4.2
60°-70°	23.1	2.7
70°-80°	12.8	1.5
80°-90°	3.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	508.2	59.6
0°-40°	686.4	80.6
0°-60°	812.6	95.4
0°-90°	852.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	852.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	923	
5°	898	83
15°	719	199
25°	492	225
35°	286	178
45°	112	90
55°	37	36
65°	23	23
75°	12	13
85°	3	4
90°	0	



TEST NUMBER: P1259948
CATALOG NUMBER: P3AS13R259050DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	923.4
1°	923.4
2°	920.2
3°	914.9
4°	907.5
5°	898.0
6°	886.3
7°	872.5
8°	857.6
9°	840.6
10°	822.6
11°	802.4
12°	783.3
13°	761.0
14°	739.8
15°	718.6
17.5°	659.1
20°	600.8
22.5°	545.6
25°	492.5
27.5°	440.5
30°	387.4
32.5°	337.5
35°	285.5
37.5°	237.8
40°	192.1
42.5°	149.7
45°	112.5
47.5°	83.9
50°	60.5
52.5°	45.6
55°	37.1
57.5°	34.0
60°	29.7
62.5°	26.5
65°	23.4
67.5°	20.2
70°	17.0
72.5°	14.9
75°	11.7
77.5°	9.6
80°	7.4
82.5°	5.3
85°	3.2
87.5°	1.1



TEST NUMBER: P1259948
CATALOG NUMBER: P3AS13R259050DE010 E3DLD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)