

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260564

Luminaire Tested: P3AS17R659050DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260564
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659050DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R65 optic, 5000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1411.0 lumens
Efficiency: N/A
Efficacy: 66.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260564
CATALOG NUMBER: P3AS17R659050DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1260564
 CATALOG NUMBER: P3AS17R659050DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79				79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73				73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68				68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63				63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58				58
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55				55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51				51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48				48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	332758
5°	328769
10°	316271
15°	296279
20°	266490
25°	226271
30°	176989
35°	126110
40°	82526
45°	51013
50°	25893
55°	9137
60°	8026
65°	8042
70°	7245
75°	7117
80°	7072
85°	7045

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 51013 cd/sqm



TEST NUMBER: P1260564
 CATALOG NUMBER: P3AS17R659050DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.2	9.9
10°-20°	363.2	25.7
20°-30°	424.5	30.1
30°-40°	296.6	21.0
40°-50°	130.6	9.3
50°-60°	29.1	2.1
60°-70°	14.8	1.1
70°-80°	8.9	0.6
80°-90°	3.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	927.9	65.8
0°-40°	1224.6	86.8
0°-60°	1384.2	98.1
0°-90°	1411.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1411.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1518	
5°	1494	140
15°	1305	363
25°	935	424
35°	471	297
45°	164	131
55°	24	29
65°	16	15
75°	8	9
85°	3	3
90°	0	



TEST NUMBER: P1260564
CATALOG NUMBER: P3AS17R659050DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1517.5
2.5°	1511.9
5°	1493.6
7.5°	1462.6
10°	1420.4
12.5°	1368.4
15°	1305.1
17.5°	1227.8
20°	1142.0
22.5°	1044.9
25°	935.2
27.5°	819.9
30°	699.0
32.5°	582.2
35°	471.1
37.5°	374.1
40°	288.3
42.5°	218.0
45°	164.5
47.5°	120.9
50°	75.9
52.5°	39.4
55°	23.9
57.5°	21.1
60°	18.3
62.5°	16.9
65°	15.5
67.5°	12.7
70°	11.3
72.5°	9.8
75°	8.4
77.5°	7.0
80°	5.6
82.5°	4.2
85°	2.8
87.5°	1.4
90°	0.0

(END OF REPORT)