

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259988

Luminaire Tested: P3AS13R309050DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259988
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R309050DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 5000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 685.0 lumens
Efficiency: N/A
Efficacy: 46.9 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259988

CATALOG NUMBER: P3AS13R309050DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1259988

CATALOG NUMBER: P3AS13R309050DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	74	68	64	72	67	63		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	67	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	58	54	72	63	57	54	62	57	54		61	57	53		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	234082
5°	226788
10°	204338
15°	169036
20°	130865
25°	98159
30°	71277
35°	47489
40°	29198
45°	17118
50°	10507
55°	8525
60°	7456
65°	6071
70°	5450
75°	5422
80°	4041
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17118 cd/sqm

TEST NUMBER: P1259988

CATALOG NUMBER: P3AS13R309050DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.8	13.8
10°-20°	205.1	29.9
20°-30°	186.6	27.2
30°-40°	112.8	16.5
40°-50°	45.2	6.6
50°-60°	20.0	2.9
60°-70°	12.1	1.8
70°-80°	6.6	1.0
80°-90°	1.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	486.4	71.0
0°-40°	599.2	87.5
0°-60°	664.5	97.0
0°-90°	685.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	685.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1068	
5°	1030	95
15°	745	205
25°	406	187
35°	177	113
45°	55	45
55°	22	20
65°	12	12
75°	6	7
85°	2	2
90°	0	

TEST NUMBER: P1259988

CATALOG NUMBER: P3AS13R309050DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1067.5
1°	1066.4
2°	1062.2
3°	1054.7
4°	1044.1
5°	1030.3
6°	1013.3
7°	995.3
8°	971.9
9°	945.3
10°	917.7
11°	885.8
12°	851.9
13°	817.9
14°	780.7
15°	744.6
17.5°	650.0
20°	560.8
22.5°	478.0
25°	405.7
27.5°	339.9
30°	281.5
32.5°	227.3
35°	177.4
37.5°	136.0
40°	102.0
42.5°	74.4
45°	55.2
47.5°	41.4
50°	30.8
52.5°	24.4
55°	22.3
57.5°	19.1
60°	17.0
62.5°	13.8
65°	11.7
67.5°	10.6
70°	8.5
72.5°	7.4
75°	6.4
77.5°	5.3
80°	3.2
82.5°	2.1
85°	2.1
87.5°	1.1



TEST NUMBER: P1259988

CATALOG NUMBER: P3AS13R309050DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)