

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260583

Luminaire Tested: P3AS17R709050DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260583
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R709050DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 5000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 496.0 lumens
Efficiency: N/A
Efficacy: 23.4 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260583

CATALOG NUMBER: P3AS17R709050DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1260583

CATALOG NUMBER: P3AS17R709050DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	116350
5°	114197
10°	107680
15°	97730
20°	85501
25°	72125
30°	59047
35°	45802
40°	32776
45°	20746
50°	10371
55°	6346
60°	5438
65°	5033
70°	4424
75°	4067
80°	3536
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20746 cd/sqm

TEST NUMBER: P1260583

CATALOG NUMBER: P3AS17R709050DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.4	9.8
10°-20°	119.8	24.2
20°-30°	136.4	27.5
30°-40°	106.7	21.5
40°-50°	52.4	10.6
50°-60°	16.1	3.3
60°-70°	9.6	1.9
70°-80°	5.1	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	304.6	61.4
0°-40°	411.3	82.9
0°-60°	479.9	96.7
0°-90°	496.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	496.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	531	
5°	519	48
15°	430	120
25°	298	136
35°	171	107
45°	67	52
55°	17	16
65°	10	10
75°	5	5
85°	1	2
90°	0	

TEST NUMBER: P1260583

CATALOG NUMBER: P3AS17R709050DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	530.6
2.5°	527.8
5°	518.8
7.5°	504.3
10°	483.6
12.5°	459.5
15°	430.5
17.5°	399.5
20°	366.4
22.5°	331.9
25°	298.1
27.5°	264.9
30°	233.2
32.5°	201.5
35°	171.1
37.5°	142.1
40°	114.5
42.5°	89.0
45°	66.9
47.5°	46.9
50°	30.4
52.5°	20.0
55°	16.6
57.5°	14.5
60°	12.4
62.5°	11.0
65°	9.7
67.5°	8.3
70°	6.9
72.5°	5.5
75°	4.8
77.5°	4.1
80°	2.8
82.5°	2.1
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)