

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260600

Luminaire Tested: P3AS20R159050D010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260600
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R159050D010 E3D1WH
Description: 3in Adjustable LED luminaire with, R15 optic, 5000K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2387.0 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260600

CATALOG NUMBER: P3AS20R159050D010 E3D1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1260600

CATALOG NUMBER: P3AS20R159050D010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	111	113	112	110	109	108	107	105		104	103	102		101
2	112	109	107	105	110	108	105	103	105	103	101		102	100	99		99
3	110	106	102	100	108	104	102	99	102	100	98		100	98	96		98
4	107	102	99	96	106	101	98	96	99	97	95		98	96	94		96
5	105	100	96	94	103	99	96	93	97	94	92		96	93	92		94
6	102	97	94	91	101	96	93	91	95	92	90		94	92	90		93
7	100	95	91	89	99	94	91	89	93	90	88		92	90	88		91
8	98	93	89	87	97	92	89	87	91	89	87		91	88	86		90
9	96	91	88	85	96	91	87	85	90	87	85		89	87	85		89
10	95	89	86	84	94	89	86	84	88	85	83		88	85	83		87

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4545469
5°	3706528
10°	1815241
15°	555599
20°	235290
25°	106434
30°	41475
35°	19140
40°	5954
45°	2233
50°	921
55°	344
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2233 cd/sqm

TEST NUMBER: P1260600

CATALOG NUMBER: P3AS20R159050D010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1310.7	54.9
10°-20°	804.3	33.7
20°-30°	216.0	9.1
30°-40°	47.6	2.0
40°-50°	6.6	0.3
50°-60°	1.2	0.1
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2331.0	97.7
0°-40°	2378.6	99.6
0°-60°	2386.4	100.0
0°-90°	2387.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2387.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	20729	
5°	16839	###
15°	2447	804
25°	440	216
35°	72	48
45°	7	7
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1260600

CATALOG NUMBER: P3AS20R159050D010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	20729.0
1°	20599.5
2°	20184.1
3°	19435.6
4°	18308.7
5°	16838.8
6°	15176.1
7°	13324.2
8°	11622.6
9°	9818.7
10°	8152.4
11°	6503.3
12°	5003.5
13°	3848.6
14°	3046.6
15°	2447.4
17.5°	1517.0
20°	1008.3
22.5°	678.8
25°	439.9
27.5°	260.7
30°	163.8
32.5°	110.4
35°	71.5
37.5°	39.8
40°	20.8
42.5°	11.8
45°	7.2
47.5°	4.5
50°	2.7
52.5°	1.8
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.9
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1260600
CATALOG NUMBER: P3AS20R159050D010 E3D1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)