

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260602

Luminaire Tested: P3AS20R159050D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260602
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R159050D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 5000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 939.0 lumens
Efficiency: N/A
Efficacy: 32.6 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260602

CATALOG NUMBER: P3AS20R159050D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1260602

CATALOG NUMBER: P3AS20R159050D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89
5	98	92	87	84	97	91	87	83	89	86	83		88	84	82		86
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	802151
5°	712039
10°	494469
15°	292419
20°	166544
25°	95207
30°	52692
35°	28081
40°	15543
45°	8404
50°	5254
55°	4167
60°	3552
65°	3269
70°	2885
75°	3050
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8404 cd/sqm

TEST NUMBER: P1260602

CATALOG NUMBER: P3AS20R159050D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	275.1	29.3
10°-20°	363.0	38.7
20°-30°	186.9	19.9
30°-40°	70.2	7.5
40°-50°	23.0	2.4
50°-60°	9.9	1.1
60°-70°	6.2	0.7
70°-80°	3.7	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	825.0	87.9
0°-40°	895.2	95.3
0°-60°	928.1	98.8
0°-90°	939.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	939.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3658	
5°	3235	275
15°	1288	363
25°	394	187
35°	105	70
45°	27	23
55°	11	10
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1260602

CATALOG NUMBER: P3AS20R159050D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3658.1
1°	3650.9
2°	3602.9
3°	3511.6
4°	3391.3
5°	3234.8
6°	3057.5
7°	2863.0
8°	2646.8
9°	2433.3
10°	2220.7
12.5°	1708.7
15°	1288.1
17.5°	964.3
20°	713.7
22.5°	532.8
25°	393.5
27.5°	286.8
30°	208.1
32.5°	147.4
35°	104.9
37.5°	75.1
40°	54.3
42.5°	38.9
45°	27.1
47.5°	19.9
50°	15.4
52.5°	12.7
55°	10.9
57.5°	9.0
60°	8.1
62.5°	7.2
65°	6.3
67.5°	5.4
70°	4.5
72.5°	4.5
75°	3.6
77.5°	2.7
80°	1.8
82.5°	1.8
85°	0.9
87.5°	0.0
90°	0.0

(END OF REPORT)