

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260021

Luminaire Tested: P3AS13R409050DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260021
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409050DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R40 optic, 5000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1491.0 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.59
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260021

CATALOG NUMBER: P3AS13R409050DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1260021

CATALOG NUMBER: P3AS13R409050DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	112	110	109	112	110	109	107	106	105	104		103	102	101		99	98	98	96
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		96	95	94	92
3	107	102	98	95	105	100	97	94	98	95	93		96	93	91		94	92	90	89
4	103	97	93	90	102	96	92	89	94	91	88		92	90	87		91	88	86	85
5	100	93	89	86	98	92	88	85	91	87	85		89	86	84		88	85	83	82
6	96	90	85	82	95	89	85	82	88	84	81		86	83	81		85	82	80	79
7	93	86	82	79	92	86	81	78	85	81	78		83	80	78		82	79	77	76
8	90	83	79	76	89	83	78	75	82	78	75		81	77	75		80	77	75	73
9	87	80	76	73	87	80	76	73	79	75	72		78	75	72		77	74	72	71
10	85	77	73	70	84	77	73	70	76	73	70		76	72	70		75	72	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	785047
5°	781266
10°	755809
15°	668699
20°	436278
25°	154557
30°	32790
35°	10788
40°	3950
45°	1302
50°	1092
55°	1223
60°	921
65°	1090
70°	705
75°	932
80°	1389
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 1848 cd/sqm

TEST NUMBER: P1260021

CATALOG NUMBER: P3AS13R409050DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	334.0	22.4
10°-20°	777.7	52.2
20°-30°	337.5	22.6
30°-40°	31.1	2.1
40°-50°	4.4	0.3
50°-60°	2.7	0.2
60°-70°	2.0	0.1
70°-80°	1.2	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1449.2	97.2
0°-40°	1480.3	99.3
0°-60°	1487.5	99.8
0°-90°	1491.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1491.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3580	
5°	3549	334
15°	2946	778
25°	639	337
35°	40	31
45°	4	4
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1260021

CATALOG NUMBER: P3AS13R409050DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	3580.1
2.5°	3575.9
5°	3549.3
7.5°	3493.1
10°	3394.4
12.5°	3227.8
15°	2945.6
17.5°	2477.6
20°	1869.6
22.5°	1213.9
25°	638.8
27.5°	274.8
30°	129.5
32.5°	70.0
35°	40.3
37.5°	24.4
40°	13.8
42.5°	7.4
45°	4.2
47.5°	3.2
50°	3.2
52.5°	3.2
55°	3.2
57.5°	3.2
60°	2.1
62.5°	2.1
65°	2.1
67.5°	2.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	1.1
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)