

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260629

Luminaire Tested: P3AS20R209050D010 E3D1B

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260629
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R209050D010 E3D1B
Description: 3in Adjustable LED luminaire with, R20 optic, 5000K CCT AND, 90CRI , E3D1B TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2315.0 lumens
Efficiency: N/A
Efficacy: 80.4 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260629

CATALOG NUMBER: P3AS20R209050D010 E3D1B

Luminous Intensity Polar Plot



TEST NUMBER: P1260629

CATALOG NUMBER: P3AS20R209050D010 E3D1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	114	112	110		113	111	110	108		107	106	105		104	103	102		100	100	99
2	112	109	106	104		110	107	105	103		104	102	101		101	100	98		99	98	96
3	109	105	102	99		107	104	101	98		101	99	97		99	97	95		97	95	94
4	106	101	98	95		105	100	97	95		99	96	94		97	95	93		95	93	92
5	104	98	95	92		102	98	94	92		96	93	91		95	92	90		93	91	90
6	101	96	92	89		100	95	92	89		94	91	89		93	90	88		92	89	88
7	99	93	90	87		98	93	89	87		92	89	86		91	88	86		90	87	86
8	97	91	87	85		96	91	87	85		90	87	85		89	86	84		88	86	84
9	95	89	85	83		94	89	85	83		88	85	83		87	84	83		87	84	82
10	93	87	84	81		92	87	83	81		86	83	81		86	83	81		85	83	81

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3511670
5°	2956651
10°	1846704
15°	690401
20°	236994
25°	98764
30°	46513
35°	20826
40°	9847
45°	5055
50°	1842
55°	344
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5055 cd/sqm

TEST NUMBER: P1260629

CATALOG NUMBER: P3AS20R209050D010 E3D1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1117.0	48.3
10°-20°	920.1	39.7
20°-30°	209.1	9.0
30°-40°	53.2	2.3
40°-50°	13.4	0.6
50°-60°	1.7	0.1
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2246.1	97.0
0°-40°	2299.4	99.3
0°-60°	2314.4	100.0
0°-90°	2315.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2315.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16014	
5°	13432	###
15°	3041	920
25°	408	209
35°	78	53
45°	16	13
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1260629

CATALOG NUMBER: P3AS20R209050D010 E3D1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	16014.5
1°	15878.7
2°	15478.6
3°	14904.8
4°	14200.6
5°	13432.1
6°	12575.9
7°	11630.9
8°	10528.5
9°	9436.0
10°	8293.7
11°	7078.1
12°	5864.3
13°	4836.1
14°	3853.1
15°	3041.2
16°	2400.4
17°	1893.5
18°	1521.5
19°	1237.3
20°	1015.6
21°	849.0
22°	708.7
23°	589.2
24°	491.5
25°	408.2
27.5°	267.0
30°	183.7
32.5°	113.1
35°	77.8
37.5°	49.8
40°	34.4
42.5°	23.5
45°	16.3
47.5°	10.9
50°	5.4
52.5°	2.7
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.9
67.5°	0.0
70°	0.0
72.5°	0.0

TEST NUMBER: P1260629

CATALOG NUMBER: P3AS20R209050D010 E3D1B

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)