

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260653

Luminaire Tested: P3AS20R259050D010 E3CD1MMS

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1260653  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R259050D010 E3CD1MMS  
Description: 3in Adjustable LED luminaire with, R25 optic, 5000K CCT AND, 90CRI , E3CD1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2349.9 lumens  
Efficiency: N/A  
Efficacy: 81.6 lumens/watt  
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1260653  
CATALOG NUMBER: P3AS20R259050D010 E3CD1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P1260653

CATALOG NUMBER: P3AS20R259050D010 E3CD1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99	100
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	97	97	97	97
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96	96	96	96	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89	89
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87	87
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	86	85	85	85	85
7	97	91	88	85	96	91	87	85	90	87	84	89	86	84	88	85	83	83	83	83	83
8	95	89	85	83	94	89	85	82	88	84	82	87	84	82	86	83	81	81	81	81	81
9	93	87	83	80	92	86	83	80	86	82	80	85	82	80	84	82	80	79	79	79	79
10	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	80	78	77	77	77	77

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2512496
5°	2330260
10°	1807159
15°	906157
20°	297713
25°	118386
30°	44412
35°	12849
40°	5811
45°	2295
50°	1876
55°	1415
60°	1623
65°	1920
70°	1154
75°	1525
80°	2273
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2295 cd/sqm



TEST NUMBER: P1260653  
 CATALOG NUMBER: P3AS20R259050D010 E3CD1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	931.2	39.6
10°-20°	1110.9	47.3
20°-30°	250.4	10.7
30°-40°	40.6	1.7
40°-50°	7.3	0.3
50°-60°	3.9	0.2
60°-70°	3.4	0.1
70°-80°	1.9	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2292.5	97.6
0°-40°	2333.1	99.3
0°-60°	2344.3	99.8
0°-90°	2349.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2349.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11458	
5°	10586	931
15°	3992	1111
25°	489	250
35°	48	41
45°	7	7
55°	4	4
65°	4	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1260653  
CATALOG NUMBER: P3AS20R259050D010 E3CD1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	11457.9
1°	11439.4
2°	11347.1
3°	11177.2
4°	10920.6
5°	10586.4
6°	10187.6
7°	9755.6
8°	9260.8
9°	8719.9
10°	8116.1
11°	7420.1
12°	6618.8
13°	5780.6
14°	4881.5
15°	3991.6
17.5°	2274.6
20°	1275.8
22.5°	769.9
25°	489.3
27.5°	300.9
30°	175.4
32.5°	92.3
35°	48.0
37.5°	31.4
40°	20.3
42.5°	12.9
45°	7.4
47.5°	5.5
50°	5.5
52.5°	5.5
55°	3.7
57.5°	3.7
60°	3.7
62.5°	3.7
65°	3.7
67.5°	3.7
70°	1.8
72.5°	1.8
75°	1.8
77.5°	1.8
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1260653  
CATALOG NUMBER: P3AS20R259050D010 E3CD1MMS

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)