

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260073

Luminaire Tested: P3AS13R459050DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260073
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R459050DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 5000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 766.0 lumens
Efficiency: N/A
Efficacy: 52.5 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260073
CATALOG NUMBER: P3AS13R459050DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1260073
 CATALOG NUMBER: P3AS13R459050DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86				86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79				79
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74				74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69				69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64				64
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60				60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56				56
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53				53
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50				50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	228162
5°	222958
10°	205674
15°	178843
20°	146919
25°	114321
30°	84418
35°	59401
40°	37069
45°	20095
50°	10882
55°	9328
60°	8377
65°	7160
70°	6155
75°	6270
80°	5304
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20095 cd/sqm



TEST NUMBER: P1260073
 CATALOG NUMBER: P3AS13R459050DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.8	12.2
10°-20°	217.8	28.4
20°-30°	216.2	28.2
30°-40°	139.2	18.2
40°-50°	53.6	7.0
50°-60°	21.8	2.8
60°-70°	13.8	1.8
70°-80°	7.4	1.0
80°-90°	2.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	527.8	68.9
0°-40°	667.1	87.1
0°-60°	742.5	96.9
0°-90°	766.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	766.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1040	
5°	1013	94
15°	788	218
25°	472	216
35°	222	139
45°	65	54
55°	24	22
65°	14	14
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1260073
CATALOG NUMBER: P3AS13R459050DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1040.5
2.5°	1035.2
5°	1012.9
7.5°	974.7
10°	923.7
12.5°	860.0
15°	787.8
17.5°	709.2
20°	629.6
22.5°	548.9
25°	472.5
27.5°	400.3
30°	333.4
32.5°	275.0
35°	221.9
37.5°	174.1
40°	129.5
42.5°	93.4
45°	64.8
47.5°	43.5
50°	31.9
52.5°	26.5
55°	24.4
57.5°	21.2
60°	19.1
62.5°	15.9
65°	13.8
67.5°	11.7
70°	9.6
72.5°	8.5
75°	7.4
77.5°	5.3
80°	4.2
82.5°	3.2
85°	2.1
87.5°	1.1
90°	0.0

(END OF REPORT)