

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260659

Luminaire Tested: P3AS20R259050D010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260659
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R259050D010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 5000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2496.0 lumens
Efficiency: N/A
Efficacy: 86.7 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260659

CATALOG NUMBER: P3AS20R259050D010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1260659

CATALOG NUMBER: P3AS20R259050D010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97	97	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92
4	106	101	97	94	104	100	96	94	98	95	92	96	93	91	94	92	90	89	89	89
5	103	97	93	91	101	96	93	90	95	92	90	93	91	89	92	90	88	87	87	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	85	85
7	98	92	88	85	97	91	87	85	90	87	84	89	86	84	88	86	84	83	83	83
8	95	89	85	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81	81	81
9	93	87	83	81	92	86	83	80	86	83	80	85	82	80	84	82	80	79	79	79
10	91	85	81	79	90	84	81	79	84	81	78	83	80	78	83	80	78	77	77	77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2733597
5°	2532285
10°	1959260
15°	935806
20°	308540
25°	130072
30°	50413
35°	21790
40°	7242
45°	3380
50°	1228
55°	688
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3380 cd/sqm

TEST NUMBER: P1260659

CATALOG NUMBER: P3AS20R259050D010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1011.2	40.5
10°-20°	1150.1	46.1
20°-30°	267.3	10.7
30°-40°	56.1	2.2
40°-50°	9.1	0.4
50°-60°	1.5	0.1
60°-70°	0.8	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2428.6	97.3
0°-40°	2484.7	99.5
0°-60°	2495.2	100.0
0°-90°	2496.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2496.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12466	
5°	11504	###
15°	4122	1150
25°	538	267
35°	81	56
45°	11	9
55°	2	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1260659

CATALOG NUMBER: P3AS20R259050D010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	12466.2
1°	12440.8
2°	12311.4
3°	12129.5
4°	11851.7
5°	11504.2
6°	11058.0
7°	10591.0
8°	10067.0
9°	9476.1
10°	8799.2
11°	8014.5
12°	7114.1
13°	6127.6
14°	5096.0
15°	4122.2
16°	3260.7
17°	2540.3
18°	1998.2
19°	1598.2
20°	1322.2
21°	1105.0
22°	927.6
23°	774.7
24°	648.0
25°	537.6
27.5°	318.6
30°	199.1
32.5°	127.6
35°	81.4
37.5°	48.9
40°	25.3
42.5°	16.3
45°	10.9
47.5°	6.3
50°	3.6
52.5°	1.8
55°	1.8
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.9
67.5°	0.9
70°	0.0
72.5°	0.0



TEST NUMBER: P1260659

CATALOG NUMBER: P3AS20R259050D010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)