

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260092

Luminaire Tested: P3AS13R509050DE010 E3DLD1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1260092  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R509050DE010 E3DLD1H  
Description: 3in Adjustable LED luminaire with, R50 optic, 5000K CCT AND, 90CRI , E3DLD1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 930.0 lumens  
Efficiency: N/A  
Efficacy: 63.7 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1260092  
CATALOG NUMBER: P3AS13R509050DE010 E3DLD1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1260092  
 CATALOG NUMBER: P3AS13R509050DE010 E3DLD1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83			83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			75
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69			69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53			53
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43			43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	188998
5°	186220
10°	177975
15°	164814
20°	148110
25°	130193
30°	110726
35°	89784
40°	67441
45°	43446
50°	20639
55°	16248
60°	15350
65°	14321
70°	12951
75°	11692
80°	10734
85°	10567

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 43446 cd/sqm



TEST NUMBER: P1260092  
 CATALOG NUMBER: P3AS13R509050DE010 E3DLD1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	79.3	8.5
10°-20°	202.4	21.8
20°-30°	245.9	26.4
30°-40°	208.6	22.4
40°-50°	108.3	11.6
50°-60°	39.1	4.2
60°-70°	27.1	2.9
70°-80°	14.7	1.6
80°-90°	4.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	527.6	56.7
0°-40°	736.2	79.2
0°-60°	883.6	95.0
0°-90°	930.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	930.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	862	
5°	846	79
15°	726	202
25°	538	246
35°	335	209
45°	140	108
55°	42	39
65°	28	27
75°	14	15
85°	4	5
90°	0	



TEST NUMBER: P1260092  
CATALOG NUMBER: P3AS13R509050DE010 E3DLD1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	861.9
2.5°	858.7
5°	846.0
7.5°	826.9
10°	799.3
12.5°	764.2
15°	726.0
17.5°	682.5
20°	634.7
22.5°	585.9
25°	538.1
27.5°	488.3
30°	437.3
32.5°	386.4
35°	335.4
37.5°	285.5
40°	235.6
42.5°	187.9
45°	140.1
47.5°	93.4
50°	60.5
52.5°	46.7
55°	42.5
57.5°	38.2
60°	35.0
62.5°	30.8
65°	27.6
67.5°	23.4
70°	20.2
72.5°	17.0
75°	13.8
77.5°	10.6
80°	8.5
82.5°	6.4
85°	4.2
87.5°	2.1
90°	0.0

(END OF REPORT)