

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260149

Luminaire Tested: P3AS13R609050DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260149
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609050DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 5000K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 429.0 lumens
Efficiency: N/A
Efficacy: 29.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260149

CATALOG NUMBER: P3AS13R609050DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1260149

CATALOG NUMBER: P3AS13R609050DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	76156
5°	75302
10°	72700
15°	68672
20°	63309
25°	57318
30°	50894
35°	43500
40°	34579
45°	24375
50°	14567
55°	7378
60°	7061
65°	6486
70°	6027
75°	5761
80°	5304
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24375 cd/sqm

TEST NUMBER: P1260149

CATALOG NUMBER: P3AS13R609050DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.1	7.5
10°-20°	84.5	19.7
20°-30°	108.6	25.3
30°-40°	100.7	23.5
40°-50°	61.3	14.3
50°-60°	20.4	4.8
60°-70°	12.4	2.9
70°-80°	7.0	1.6
80°-90°	2.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	225.2	52.5
0°-40°	325.9	76.0
0°-60°	407.6	95.0
0°-90°	429.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	429.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	347	
5°	342	32
15°	302	85
25°	237	109
35°	162	101
45°	79	61
55°	19	20
65°	12	12
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1260149

CATALOG NUMBER: P3AS13R609050DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	347.3
2.5°	345.7
5°	342.1
7.5°	335.3
10°	326.5
12.5°	315.5
15°	302.5
17.5°	287.4
20°	271.3
22.5°	254.1
25°	236.9
27.5°	219.2
30°	201.0
32.5°	182.8
35°	162.5
37.5°	141.1
40°	120.8
42.5°	99.4
45°	78.6
47.5°	60.9
50°	42.7
52.5°	25.5
55°	19.3
57.5°	17.7
60°	16.1
62.5°	14.1
65°	12.5
67.5°	10.9
70°	9.4
72.5°	7.8
75°	6.8
77.5°	5.2
80°	4.2
82.5°	2.6
85°	1.6
87.5°	1.0
90°	0.0

(END OF REPORT)