

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260158

Luminaire Tested: P3AS13R609050DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260158
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609050DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R60 optic, 5000K CCT AND, 90CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 772.0 lumens
Efficiency: N/A
Efficacy: 52.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260158

CATALOG NUMBER: P3AS13R609050DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1260158

CATALOG NUMBER: P3AS13R609050DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	195642
5°	191261
10°	179066
15°	160637
20°	138145
25°	114224
30°	90267
35°	67030
40°	46172
45°	28964
50°	15931
55°	9328
60°	8377
65°	7160
70°	6091
75°	6270
80°	5304
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 28964 cd/sqm

TEST NUMBER: P1260158

CATALOG NUMBER: P3AS13R609050DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.9	10.5
10°-20°	196.5	25.5
20°-30°	215.6	27.9
30°-40°	157.1	20.3
40°-50°	74.2	9.6
50°-60°	24.3	3.1
60°-70°	13.8	1.8
70°-80°	7.4	1.0
80°-90°	2.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	493.0	63.9
0°-40°	650.0	84.2
0°-60°	748.5	97.0
0°-90°	772.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	772.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	892	
5°	869	81
15°	708	197
25°	472	216
35°	250	157
45°	93	74
55°	24	24
65°	14	14
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1260158

CATALOG NUMBER: P3AS13R609050DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	892.2
2.5°	886.9
5°	868.9
7.5°	841.3
10°	804.2
12.5°	759.6
15°	707.6
17.5°	651.4
20°	592.0
22.5°	531.5
25°	472.1
27.5°	412.7
30°	356.5
32.5°	302.4
35°	250.4
37.5°	203.7
40°	161.3
42.5°	124.1
45°	93.4
47.5°	67.9
50°	46.7
52.5°	30.8
55°	24.4
57.5°	21.2
60°	19.1
62.5°	15.9
65°	13.8
67.5°	11.7
70°	9.5
72.5°	8.5
75°	7.4
77.5°	5.3
80°	4.2
82.5°	3.2
85°	2.1
87.5°	1.1
90°	0.0

(END OF REPORT)