

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260772

Luminaire Tested: P3AS20R459050D010 E3CB1MW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1260772  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R459050D010 E3CB1MW  
Description: 3in Adjustable LED luminaire with, R45 optic, 5000K CCT AND, 90CRI , E3CB1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2475.9 lumens  
Efficiency: N/A  
Efficacy: 86.0 lumens/watt  
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1260772

CATALOG NUMBER: P3AS20R459050D010 E3CB1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1260772

CATALOG NUMBER: P3AS20R459050D010 E3CB1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 |  | 102 | 101 | 100 |  | 99  |
| 2   | 110 | 106 | 102 | 100 | 108 | 104 | 101 | 98  | 101 | 98  | 96  |  | 98  | 96  | 94  |  | 95  |
| 3   | 106 | 100 | 96  | 93  | 104 | 99  | 95  | 92  | 96  | 93  | 91  |  | 94  | 91  | 89  |  | 92  |
| 4   | 102 | 95  | 91  | 87  | 100 | 94  | 90  | 87  | 92  | 89  | 86  |  | 90  | 87  | 85  |  | 88  |
| 5   | 98  | 91  | 86  | 82  | 96  | 90  | 85  | 82  | 88  | 84  | 81  |  | 87  | 83  | 81  |  | 85  |
| 6   | 94  | 87  | 82  | 78  | 93  | 86  | 81  | 78  | 85  | 80  | 77  |  | 83  | 80  | 77  |  | 82  |
| 7   | 90  | 83  | 78  | 74  | 89  | 82  | 78  | 74  | 81  | 77  | 74  |  | 80  | 76  | 74  |  | 79  |
| 8   | 87  | 79  | 74  | 71  | 86  | 79  | 74  | 71  | 78  | 74  | 71  |  | 77  | 73  | 70  |  | 76  |
| 9   | 84  | 76  | 71  | 68  | 83  | 76  | 71  | 68  | 75  | 71  | 68  |  | 74  | 70  | 67  |  | 73  |
| 10  | 81  | 73  | 68  | 65  | 80  | 73  | 68  | 65  | 72  | 68  | 65  |  | 71  | 67  | 65  |  | 71  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1073489 |
| 5°  | 1079218 |
| 10° | 1046051 |
| 15° | 876577  |
| 20° | 670075  |
| 25° | 407927  |
| 30° | 169722  |
| 35° | 54368   |
| 40° | 16917   |
| 45° | 3442    |
| 50° | 2524    |
| 55° | 2829    |
| 60° | 2412    |
| 65° | 2854    |
| 70° | 2372    |
| 75° | 3135    |
| 80° | 2273    |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3442 cd/sqm

TEST NUMBER: P1260772

CATALOG NUMBER: P3AS20R459050D010 E3CB1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 462.4  | 18.7      |
| 10°-20°   | 1061.3 | 42.9      |
| 20°-30°   | 764.1  | 30.9      |
| 30°-40°   | 159.0  | 6.4       |
| 40°-50°   | 14.5   | 0.6       |
| 50°-60°   | 6.0    | 0.2       |
| 60°-70°   | 4.8    | 0.2       |
| 70°-80°   | 3.2    | 0.1       |
| 80°-90°   | 0.7    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2287.8 | 92.4      |
| 0°-40°    | 2446.8 | 98.8      |
| 0°-60°    | 2467.3 | 99.7      |
| 0°-90°    | 2475.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2475.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 4896 |      |
| 5°  | 4903 | 462  |
| 15° | 3861 | 1061 |
| 25° | 1686 | 764  |
| 35° | 203  | 159  |
| 45° | 11   | 15   |
| 55° | 7    | 6    |
| 65° | 6    | 5    |
| 75° | 4    | 3    |
| 85° | 0    | 1    |
| 90° | 0    |      |

TEST NUMBER: P1260772

CATALOG NUMBER: P3AS20R459050D010 E3CB1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 4895.5 |
| 2.5°  | 4897.3 |
| 5°    | 4902.9 |
| 7.5°  | 4867.8 |
| 10°   | 4697.9 |
| 12.5° | 4343.3 |
| 15°   | 3861.3 |
| 17.5° | 3368.3 |
| 20°   | 2871.5 |
| 22.5° | 2300.9 |
| 25°   | 1686.0 |
| 27.5° | 1111.7 |
| 30°   | 670.3  |
| 32.5° | 374.9  |
| 35°   | 203.1  |
| 37.5° | 114.5  |
| 40°   | 59.1   |
| 42.5° | 25.9   |
| 45°   | 11.1   |
| 47.5° | 7.4    |
| 50°   | 7.4    |
| 52.5° | 7.4    |
| 55°   | 7.4    |
| 57.5° | 5.5    |
| 60°   | 5.5    |
| 62.5° | 5.5    |
| 65°   | 5.5    |
| 67.5° | 3.7    |
| 70°   | 3.7    |
| 72.5° | 3.7    |
| 75°   | 3.7    |
| 77.5° | 1.8    |
| 80°   | 1.8    |
| 82.5° | 1.8    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)