

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260776

Luminaire Tested: P3AS20R459050D010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260776
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R459050D010 E3D1MW
Description: 3in Adjustable LED luminaire with, R45 optic, 5000K CCT AND, 90CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2475.9 lumens
Efficiency: N/A
Efficacy: 86.0 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260776
CATALOG NUMBER: P3AS20R459050D010 E3D1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1260776
 CATALOG NUMBER: P3AS20R459050D010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	95
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	94	92	91
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	92	90	88	87
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87	92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82	88	86	84	82
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79	85	82	80	79
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75	82	79	76	75
7	90	83	78	74	89	82	78	74	81	77	74	80	76	74	79	76	73	72	79	76	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	76	73	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	64	71	67	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1073489
5°	1079218
10°	1046051
15°	876577
20°	670075
25°	407927
30°	169722
35°	54368
40°	16917
45°	3442
50°	2524
55°	2829
60°	2412
65°	2854
70°	2372
75°	3135
80°	2273
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3442 cd/sqm



TEST NUMBER: P1260776
 CATALOG NUMBER: P3AS20R459050D010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	462.4	18.7
10°-20°	1061.3	42.9
20°-30°	764.1	30.9
30°-40°	159.0	6.4
40°-50°	14.5	0.6
50°-60°	6.0	0.2
60°-70°	4.8	0.2
70°-80°	3.2	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2287.8	92.4
0°-40°	2446.8	98.8
0°-60°	2467.3	99.7
0°-90°	2475.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2475.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4896	
5°	4903	462
15°	3861	1061
25°	1686	764
35°	203	159
45°	11	15
55°	7	6
65°	6	5
75°	4	3
85°	0	1
90°	0	



TEST NUMBER: P1260776
CATALOG NUMBER: P3AS20R459050D010 E3D1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4895.5
2.5°	4897.3
5°	4902.9
7.5°	4867.8
10°	4697.9
12.5°	4343.3
15°	3861.3
17.5°	3368.3
20°	2871.5
22.5°	2300.9
25°	1686.0
27.5°	1111.7
30°	670.3
32.5°	374.9
35°	203.1
37.5°	114.5
40°	59.1
42.5°	25.9
45°	11.1
47.5°	7.4
50°	7.4
52.5°	7.4
55°	7.4
57.5°	5.5
60°	5.5
62.5°	5.5
65°	5.5
67.5°	3.7
70°	3.7
72.5°	3.7
75°	3.7
77.5°	1.8
80°	1.8
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)