

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260184

Luminaire Tested: P3AS13R659050DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260184
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659050DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 5000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 361.0 lumens
Efficiency: N/A
Efficacy: 24.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260184

CATALOG NUMBER: P3AS13R659050DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1260184

CATALOG NUMBER: P3AS13R659050DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		90
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	91769
5°	89478
10°	83321
15°	74666
20°	64499
25°	53640
30°	42310
35°	31347
40°	21612
45°	13397
50°	7266
55°	4588
60°	3859
65°	3528
70°	3013
75°	2626
80°	2652
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13397 cd/sqm

TEST NUMBER: P1260184

CATALOG NUMBER: P3AS13R659050DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.8	10.5
10°-20°	91.4	25.3
20°-30°	101.1	28.0
30°-40°	73.4	20.3
40°-50°	34.4	9.5
50°-60°	11.6	3.2
60°-70°	6.7	1.9
70°-80°	3.5	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	230.3	63.8
0°-40°	303.7	84.1
0°-60°	349.7	96.9
0°-90°	361.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	361.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	418	
5°	406	38
15°	329	91
25°	222	101
35°	117	73
45°	43	34
55°	12	12
65°	7	7
75°	3	4
85°	1	1
90°	0	

TEST NUMBER: P1260184

CATALOG NUMBER: P3AS13R659050DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	418.5
2.5°	415.9
5°	406.5
7.5°	392.4
10°	374.2
12.5°	352.9
15°	328.9
17.5°	302.9
20°	276.4
22.5°	248.8
25°	221.7
27.5°	194.1
30°	167.1
32.5°	141.0
35°	117.1
37.5°	95.2
40°	75.5
42.5°	57.8
45°	43.2
47.5°	31.2
50°	21.3
52.5°	14.6
55°	12.0
57.5°	10.4
60°	8.8
62.5°	7.8
65°	6.8
67.5°	5.7
70°	4.7
72.5°	4.2
75°	3.1
77.5°	2.6
80°	2.1
82.5°	1.6
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)