

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260779

Luminaire Tested: P3AS20R459050D010 E3DL1LI

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1260779  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R459050D010 E3DL1LI  
Description: 3in Adjustable LED luminaire with, R45 optic, 5000K CCT AND, 90CRI , E3DL1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2063.9 lumens  
Efficiency: N/A  
Efficacy: 71.7 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1260779

CATALOG NUMBER: P3AS20R459050D010 E3DL1LI

### Luminous Intensity Polar Plot



TEST NUMBER: P1260779

CATALOG NUMBER: P3AS20R459050D010 E3DL1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 |  | 101 | 100 | 99  |  | 98  |
| 2   | 109 | 104 | 100 | 97  | 106 | 102 | 99  | 96  | 99  | 96  | 94  |  | 96  | 94  | 92  |  | 93  |
| 3   | 104 | 98  | 93  | 89  | 102 | 96  | 92  | 88  | 94  | 90  | 87  |  | 91  | 88  | 86  |  | 89  |
| 4   | 99  | 92  | 87  | 83  | 97  | 91  | 86  | 82  | 89  | 85  | 81  |  | 87  | 83  | 80  |  | 85  |
| 5   | 94  | 87  | 81  | 77  | 93  | 86  | 81  | 77  | 84  | 80  | 76  |  | 82  | 79  | 76  |  | 81  |
| 6   | 90  | 82  | 77  | 73  | 89  | 81  | 76  | 72  | 80  | 75  | 72  |  | 78  | 74  | 71  |  | 77  |
| 7   | 86  | 78  | 72  | 68  | 85  | 77  | 72  | 68  | 76  | 71  | 68  |  | 75  | 71  | 67  |  | 74  |
| 8   | 83  | 74  | 68  | 65  | 82  | 73  | 68  | 65  | 72  | 68  | 64  |  | 71  | 67  | 64  |  | 70  |
| 9   | 79  | 70  | 65  | 61  | 78  | 70  | 65  | 61  | 69  | 64  | 61  |  | 68  | 64  | 61  |  | 67  |
| 10  | 76  | 67  | 62  | 58  | 75  | 67  | 62  | 58  | 66  | 61  | 58  |  | 65  | 61  | 58  |  | 65  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 775113 |
| 5°  | 756943 |
| 10° | 695823 |
| 15° | 589583 |
| 20° | 457443 |
| 25° | 319760 |
| 30° | 201449 |
| 35° | 118588 |
| 40° | 67097  |
| 45° | 32624  |
| 50° | 11326  |
| 55° | 9175   |
| 60° | 8903   |
| 65° | 8613   |
| 70° | 8271   |
| 75° | 7795   |
| 80° | 6945   |
| 85° | 4529   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 32624 cd/sqm

TEST NUMBER: P1260779

CATALOG NUMBER: P3AS20R459050D010 E3DL1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 318.3  | 15.4      |
| 10°-20°   | 713.2  | 34.6      |
| 20°-30°   | 605.6  | 29.3      |
| 30°-40°   | 288.9  | 14.0      |
| 40°-50°   | 87.0   | 4.2       |
| 50°-60°   | 22.0   | 1.1       |
| 60°-70°   | 16.5   | 0.8       |
| 70°-80°   | 9.7    | 0.5       |
| 80°-90°   | 2.7    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 1637.1 | 79.3      |
| 0°-40°    | 1926.0 | 93.3      |
| 0°-60°    | 2035.0 | 98.6      |
| 0°-90°    | 2063.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2063.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3535 |      |
| 5°  | 3439 | 318  |
| 15° | 2597 | 713  |
| 25° | 1322 | 606  |
| 35° | 443  | 289  |
| 45° | 105  | 87   |
| 55° | 24   | 22   |
| 65° | 17   | 16   |
| 75° | 9    | 10   |
| 85° | 2    | 3    |
| 90° | 0    |      |

TEST NUMBER: P1260779

CATALOG NUMBER: P3AS20R459050D010 E3DL1LI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 3534.8 |
| 2.5°  | 3512.6 |
| 5°    | 3438.8 |
| 7.5°  | 3311.4 |
| 10°   | 3125.0 |
| 12.5° | 2877.6 |
| 15°   | 2597.1 |
| 17.5° | 2285.1 |
| 20°   | 1960.3 |
| 22.5° | 1629.9 |
| 25°   | 1321.6 |
| 27.5° | 1041.0 |
| 30°   | 795.6  |
| 32.5° | 598.0  |
| 35°   | 443.0  |
| 37.5° | 326.7  |
| 40°   | 234.4  |
| 42.5° | 162.4  |
| 45°   | 105.2  |
| 47.5° | 59.1   |
| 50°   | 33.2   |
| 52.5° | 25.8   |
| 55°   | 24.0   |
| 57.5° | 22.1   |
| 60°   | 20.3   |
| 62.5° | 18.5   |
| 65°   | 16.6   |
| 67.5° | 14.8   |
| 70°   | 12.9   |
| 72.5° | 11.1   |
| 75°   | 9.2    |
| 77.5° | 7.4    |
| 80°   | 5.5    |
| 82.5° | 3.7    |
| 85°   | 1.8    |
| 87.5° | 1.8    |
| 90°   | 0.0    |

(END OF REPORT)