

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260188

Luminaire Tested: P3AS13R659050DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260188
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659050DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R65 optic, 5000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1065.0 lumens
Efficiency: N/A
Efficacy: 72.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260188

CATALOG NUMBER: P3AS13R659050DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1260188

CATALOG NUMBER: P3AS13R659050DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	251164
5°	248139
10°	238717
15°	223634
20°	201127
25°	170792
30°	133590
35°	95191
40°	62288
45°	38516
50°	19547
55°	6881
60°	6052
65°	6071
70°	5450
75°	5422
80°	5304
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 38516 cd/sqm

TEST NUMBER: P1260188

CATALOG NUMBER: P3AS13R659050DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.8	9.9
10°-20°	274.2	25.7
20°-30°	320.4	30.1
30°-40°	223.9	21.0
40°-50°	98.5	9.3
50°-60°	21.9	2.1
60°-70°	11.2	1.0
70°-80°	6.7	0.6
80°-90°	2.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	700.4	65.8
0°-40°	924.3	86.8
0°-60°	1044.8	98.1
0°-90°	1065.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1065.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1145	
5°	1127	106
15°	985	274
25°	706	320
35°	356	224
45°	124	99
55°	18	22
65°	12	11
75°	6	7
85°	2	2
90°	0	

TEST NUMBER: P1260188

CATALOG NUMBER: P3AS13R659050DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1145.4
2.5°	1141.1
5°	1127.3
7.5°	1104.0
10°	1072.1
12.5°	1032.9
15°	985.1
17.5°	926.7
20°	861.9
22.5°	788.7
25°	705.9
27.5°	618.9
30°	527.6
32.5°	439.5
35°	355.6
37.5°	282.4
40°	217.6
42.5°	164.5
45°	124.2
47.5°	91.3
50°	57.3
52.5°	29.7
55°	18.0
57.5°	15.9
60°	13.8
62.5°	12.7
65°	11.7
67.5°	9.6
70°	8.5
72.5°	7.4
75°	6.4
77.5°	5.3
80°	4.2
82.5°	3.2
85°	2.1
87.5°	1.1
90°	0.0

(END OF REPORT)