

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260192

Luminaire Tested: P3AS13R709050DE010 E3CB1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260192
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709050DE010 E3CB1MW
Description: 3in Adjustable LED luminaire with, R70 optic, 5000K CCT AND, 90CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1328.0 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260192
CATALOG NUMBER: P3AS13R709050DE010 E3CB1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1260192
 CATALOG NUMBER: P3AS13R709050DE010 E3CB1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78			78
4	95	87	81	77	94	86	81	76	84	79	75	82	78	75	80	77	74	72			72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	76	66	59	55	75	65	59	55	64	58	55	63	58	54	62	57	54	53			53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	50	58	54	50	49			49
10	68	58	52	47	67	57	51	47	56	51	47	56	51	47	55	50	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	263707
5°	251617
10°	239408
15°	233009
20°	224393
25°	212383
30°	197524
35°	165942
40°	106943
45°	49711
50°	13032
55°	3250
60°	3245
65°	2750
70°	2693
75°	2711
80°	2652
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 49711 cd/sqm



TEST NUMBER: P1260192
 CATALOG NUMBER: P3AS13R709050DE010 E3CB1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.0	8.1
10°-20°	288.4	21.7
20°-30°	402.9	30.3
30°-40°	373.6	28.1
40°-50°	133.9	10.1
50°-60°	11.3	0.9
60°-70°	5.6	0.4
70°-80°	3.6	0.3
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	798.3	60.1
0°-40°	1172.0	88.3
0°-60°	1317.2	99.2
0°-90°	1328.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1328.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1203	
5°	1143	107
15°	1026	288
25°	878	403
35°	620	374
45°	160	134
55°	8	11
65°	5	6
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P1260192
CATALOG NUMBER: P3AS13R709050DE010 E3CB1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1202.6
2.5°	1184.5
5°	1143.1
7.5°	1104.9
10°	1075.2
12.5°	1050.8
15°	1026.4
17.5°	996.7
20°	961.6
22.5°	921.3
25°	877.8
27.5°	833.2
30°	780.1
32.5°	712.2
35°	619.9
37.5°	502.1
40°	373.6
42.5°	254.7
45°	160.3
47.5°	89.2
50°	38.2
52.5°	12.7
55°	8.5
57.5°	7.4
60°	7.4
62.5°	6.4
65°	5.3
67.5°	5.3
70°	4.2
72.5°	4.2
75°	3.2
77.5°	3.2
80°	2.1
82.5°	2.1
85°	1.1
87.5°	1.1
90°	0.0

(END OF REPORT)