

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260232

Luminaire Tested: P3AS17R129050DE010 E3DL1LI

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1260232  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R129050DE010 E3DL1LI  
Description: 3in Adjustable LED luminaire with, R12 optic, 5000K CCT AND, 90CRI , E3DL1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1203.0 lumens  
Efficiency: N/A  
Efficacy: 52.5 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 22.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1260232  
CATALOG NUMBER: P3AS17R129050DE010 E3DL1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1260232  
 CATALOG NUMBER: P3AS17R129050DE010 E3DL1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	87	87	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	80	80	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77	77	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	74	74	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	72	72	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69	69	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67	67	67

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1027681
5°	912214
10°	633500
15°	374645
20°	213379
25°	121967
30°	67479
35°	35978
40°	19894
45°	10792
50°	6720
55°	5314
60°	4561
65°	4203
70°	3719
75°	3897
80°	2904
85°	3019

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10792 cd/sqm



TEST NUMBER: P1260232  
 CATALOG NUMBER: P3AS17R129050DE010 E3DL1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	352.4	29.3
10°-20°	465.1	38.7
20°-30°	239.5	19.9
30°-40°	89.9	7.5
40°-50°	29.4	2.4
50°-60°	12.6	1.1
60°-70°	8.0	0.7
70°-80°	4.7	0.4
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1057.0	87.9
0°-40°	1146.9	95.3
0°-60°	1189.0	98.8
0°-90°	1203.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1203.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4687	
5°	4144	352
15°	1650	465
25°	504	239
35°	134	90
45°	35	29
55°	14	13
65°	8	8
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1260232  
CATALOG NUMBER: P3AS17R129050DE010 E3DL1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4686.6
1°	4677.3
2°	4615.9
3°	4498.8
4°	4344.7
5°	4144.2
6°	3917.1
7°	3667.9
8°	3390.9
9°	3117.4
10°	2845.1
12.5°	2189.2
15°	1650.3
17.5°	1235.4
20°	914.4
22.5°	682.6
25°	504.1
27.5°	367.4
30°	266.5
32.5°	188.9
35°	134.4
37.5°	96.2
40°	69.5
42.5°	49.8
45°	34.8
47.5°	25.5
50°	19.7
52.5°	16.2
55°	13.9
57.5°	11.6
60°	10.4
62.5°	9.3
65°	8.1
67.5°	7.0
70°	5.8
72.5°	5.8
75°	4.6
77.5°	3.5
80°	2.3
82.5°	2.3
85°	1.2
87.5°	0.0
90°	0.0

(END OF REPORT)