

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260247

Luminaire Tested: P3AS17R159050DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260247
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R159050DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R15 optic, 5000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1779.0 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260247

CATALOG NUMBER: P3AS17R159050DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1260247

CATALOG NUMBER: P3AS17R159050DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98		
2	113	110	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96		
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	97	95	94		
4	107	103	100	97	106	102	99	97	100	97	95	98	96	94	97	95	93	92		
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92	91		
6	103	98	94	92	102	97	94	92	96	93	91	95	92	91	94	92	90	89		
7	101	96	92	90	100	95	92	90	94	91	89	93	91	89	92	90	89	88		
8	99	94	90	88	98	93	90	88	92	90	88	92	89	87	91	89	87	86		
9	97	92	89	87	97	92	89	87	91	88	86	90	88	86	90	87	86	85		
10	96	90	87	85	95	90	87	85	89	87	85	89	86	85	88	86	85	84		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3457947
5°	2898099
10°	1365127
15°	411580
20°	152287
25°	59205
30°	22079
35°	6773
40°	2405
45°	1302
50°	955
55°	1070
60°	1228
65°	726
70°	898
75°	1186
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1302 cd/sqm

TEST NUMBER: P1260247

CATALOG NUMBER: P3AS17R159050DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1017.9	57.2
10°-20°	605.0	34.0
20°-30°	127.1	7.1
30°-40°	20.5	1.2
40°-50°	3.5	0.2
50°-60°	2.5	0.1
60°-70°	1.6	0.1
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1750.0	98.4
0°-40°	1770.5	99.5
0°-60°	1776.5	99.9
0°-90°	1779.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1779.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15770	
5°	13166	###
15°	1813	605
25°	245	127
35°	25	20
45°	4	3
55°	3	3
65°	1	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1260247

CATALOG NUMBER: P3AS17R159050DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	15769.5
1°	15720.3
2°	15469.9
3°	14969.2
4°	14235.0
5°	13166.1
6°	11910.1
7°	10474.1
8°	9102.8
9°	7550.0
10°	6130.9
12.5°	3308.1
15°	1813.0
17.5°	1061.9
20°	652.6
22.5°	399.4
25°	244.7
27.5°	147.7
30°	87.2
32.5°	49.2
35°	25.3
37.5°	14.1
40°	8.4
42.5°	5.6
45°	4.2
47.5°	2.8
50°	2.8
52.5°	2.8
55°	2.8
57.5°	2.8
60°	2.8
62.5°	1.4
65°	1.4
67.5°	1.4
70°	1.4
72.5°	1.4
75°	1.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)