

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260259

Luminaire Tested: P3AS17R159050DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260259
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R159050DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R15 optic, 5000K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1460.0 lumens
Efficiency: N/A
Efficacy: 68.9 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260259

CATALOG NUMBER: P3AS17R159050DE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1260259

CATALOG NUMBER: P3AS17R159050DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1247225
5°	1107107
10°	768835
15°	454668
20°	258953
25°	148025
30°	81911
35°	43687
40°	24160
45°	13087
50°	8153
55°	6461
60°	5570
65°	5085
70°	4488
75°	4745
80°	3536
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13087 cd/sqm

TEST NUMBER: P1260259

CATALOG NUMBER: P3AS17R159050DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	427.7	29.3
10°-20°	564.5	38.7
20°-30°	290.6	19.9
30°-40°	109.1	7.5
40°-50°	35.7	2.4
50°-60°	15.4	1.1
60°-70°	9.7	0.7
70°-80°	5.7	0.4
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1282.8	87.9
0°-40°	1391.9	95.3
0°-60°	1443.0	98.8
0°-90°	1460.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1460.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5688	
5°	5030	428
15°	2003	564
25°	612	291
35°	163	109
45°	42	36
55°	17	15
65°	10	10
75°	6	6
85°	1	2
90°	0	

TEST NUMBER: P1260259

CATALOG NUMBER: P3AS17R159050DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	5687.8
1°	5676.5
2°	5602.0
3°	5459.9
4°	5272.9
5°	5029.6
6°	4753.9
7°	4451.5
8°	4115.4
9°	3783.4
10°	3452.9
12.5°	2656.8
15°	2002.8
17.5°	1499.3
20°	1109.7
22.5°	828.4
25°	611.8
27.5°	445.9
30°	323.5
32.5°	229.3
35°	163.2
37.5°	116.7
40°	84.4
42.5°	60.5
45°	42.2
47.5°	30.9
50°	23.9
52.5°	19.7
55°	16.9
57.5°	14.1
60°	12.7
62.5°	11.3
65°	9.8
67.5°	8.4
70°	7.0
72.5°	7.0
75°	5.6
77.5°	4.2
80°	2.8
82.5°	2.8
85°	1.4
87.5°	0.0
90°	0.0

(END OF REPORT)