

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260852

Luminaire Tested: P3AS20R559050D010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260852
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R559050D010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 5000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1343.0 lumens
Efficiency: N/A
Efficacy: 46.6 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260852

CATALOG NUMBER: P3AS20R559050D010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1260852

CATALOG NUMBER: P3AS20R559050D010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		92
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		79
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		73
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		67
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		59
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		55
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		52
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	365344
5°	356173
10°	331123
15°	294871
20°	250575
25°	202221
30°	154176
35°	109647
40°	72364
45°	42919
50°	25176
55°	15522
60°	13771
65°	12453
70°	10643
75°	9404
80°	9345
85°	9309

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 42919 cd/sqm

TEST NUMBER: P1260852

CATALOG NUMBER: P3AS20R559050D010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.2	11.2
10°-20°	360.1	26.8
20°-30°	381.4	28.4
30°-40°	257.7	19.2
40°-50°	113.0	8.4
50°-60°	40.5	3.0
60°-70°	23.7	1.8
70°-80°	12.4	0.9
80°-90°	4.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	891.7	66.4
0°-40°	1149.5	85.6
0°-60°	1302.9	97.0
0°-90°	1343.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1343.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1666	
5°	1618	150
15°	1299	360
25°	836	381
35°	410	258
45°	138	113
55°	41	40
65°	24	24
75°	11	12
85°	4	4
90°	0	

TEST NUMBER: P1260852

CATALOG NUMBER: P3AS20R559050D010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1666.1
2.5°	1653.2
5°	1618.1
7.5°	1560.9
10°	1487.1
12.5°	1398.5
15°	1298.9
17.5°	1188.2
20°	1073.8
22.5°	953.9
25°	835.8
27.5°	719.6
30°	608.9
32.5°	503.7
35°	409.6
37.5°	324.7
40°	252.8
42.5°	190.0
45°	138.4
47.5°	101.5
50°	73.8
52.5°	51.7
55°	40.6
57.5°	36.9
60°	31.4
62.5°	27.7
65°	24.0
67.5°	20.3
70°	16.6
72.5°	14.8
75°	11.1
77.5°	9.2
80°	7.4
82.5°	5.5
85°	3.7
87.5°	1.8
90°	0.0

(END OF REPORT)