

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260262

Luminaire Tested: P3AS17R159050DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260262
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R159050DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R15 optic, 5000K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1460.0 lumens
Efficiency: N/A
Efficacy: 68.9 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260262
CATALOG NUMBER: P3AS17R159050DE010 E3DL1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1260262
 CATALOG NUMBER: P3AS17R159050DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	87	87	87	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	83	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	80	80	80	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77	77	77	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	74	74	74	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	72	72	72	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69	69	69	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67	67	67	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1247225
5°	1107107
10°	768835
15°	454668
20°	258953
25°	148025
30°	81911
35°	43687
40°	24160
45°	13087
50°	8153
55°	6461
60°	5570
65°	5085
70°	4488
75°	4745
80°	3536
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13087 cd/sqm



TEST NUMBER: P1260262
 CATALOG NUMBER: P3AS17R159050DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	427.7	29.3
10°-20°	564.5	38.7
20°-30°	290.6	19.9
30°-40°	109.1	7.5
40°-50°	35.7	2.4
50°-60°	15.4	1.1
60°-70°	9.7	0.7
70°-80°	5.7	0.4
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1282.8	87.9
0°-40°	1391.9	95.3
0°-60°	1443.0	98.8
0°-90°	1460.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1460.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5688	
5°	5030	428
15°	2003	564
25°	612	291
35°	163	109
45°	42	36
55°	17	15
65°	10	10
75°	6	6
85°	1	2
90°	0	



TEST NUMBER: P1260262
CATALOG NUMBER: P3AS17R159050DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	5687.8
1°	5676.5
2°	5602.0
3°	5459.9
4°	5272.9
5°	5029.6
6°	4753.9
7°	4451.5
8°	4115.4
9°	3783.4
10°	3452.9
12.5°	2656.8
15°	2002.8
17.5°	1499.3
20°	1109.7
22.5°	828.4
25°	611.8
27.5°	445.9
30°	323.5
32.5°	229.3
35°	163.2
37.5°	116.7
40°	84.4
42.5°	60.5
45°	42.2
47.5°	30.9
50°	23.9
52.5°	19.7
55°	16.9
57.5°	14.1
60°	12.7
62.5°	11.3
65°	9.8
67.5°	8.4
70°	7.0
72.5°	7.0
75°	5.6
77.5°	4.2
80°	2.8
82.5°	2.8
85°	1.4
87.5°	0.0
90°	0.0

(END OF REPORT)