

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260857

Luminaire Tested: P3AS20R609050D010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260857
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R609050D010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R60 optic, 5000K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2386.9 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260857

CATALOG NUMBER: P3AS20R609050D010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1260857

CATALOG NUMBER: P3AS20R609050D010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79
6	88	79	73	69	87	79	73	69	77	72	68		76	71	68		74
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70
8	80	70	64	60	78	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	569998
5°	547390
10°	563583
15°	570832
20°	504044
25°	424791
30°	344509
35°	224380
40°	103050
45°	39508
50°	13236
55°	3517
60°	3245
65°	2854
70°	2372
75°	3135
80°	2273
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 39508 cd/sqm

TEST NUMBER: P1260857

CATALOG NUMBER: P3AS20R609050D010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	239.3	10.0
10°-20°	688.6	28.8
20°-30°	803.2	33.6
30°-40°	518.3	21.7
40°-50°	116.1	4.9
50°-60°	11.6	0.5
60°-70°	5.5	0.2
70°-80°	3.2	0.1
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1731.1	72.5
0°-40°	2249.4	94.2
0°-60°	2377.1	99.6
0°-90°	2386.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2386.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2599	
5°	2487	239
15°	2514	689
25°	1756	803
35°	838	518
45°	127	116
55°	9	12
65°	6	5
75°	4	3
85°	2	1
90°	0	

TEST NUMBER: P1260857

CATALOG NUMBER: P3AS20R609050D010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2599.4
2.5°	2557.0
5°	2486.8
7.5°	2483.1
10°	2531.1
12.5°	2562.5
15°	2514.5
17.5°	2370.5
20°	2160.0
22.5°	1940.3
25°	1755.7
27.5°	1574.8
30°	1360.6
32.5°	1109.6
35°	838.2
37.5°	572.3
40°	360.0
42.5°	216.0
45°	127.4
47.5°	73.8
50°	38.8
52.5°	12.9
55°	9.2
57.5°	7.4
60°	7.4
62.5°	5.5
65°	5.5
67.5°	5.5
70°	3.7
72.5°	3.7
75°	3.7
77.5°	1.8
80°	1.8
82.5°	1.8
85°	1.8
87.5°	0.0
90°	0.0

(END OF REPORT)