

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260285

Luminaire Tested: P3AS17R209050DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260285
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R209050DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R20 optic, 5000K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1763.0 lumens
Efficiency: N/A
Efficacy: 83.2 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260285

CATALOG NUMBER: P3AS17R209050DE010 E3D1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1260285

CATALOG NUMBER: P3AS17R209050DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	114	112	110	113	111	110	108	107	106	105		104	103	102		100
2	112	109	106	104	110	107	105	103	104	102	101		101	100	98		99
3	109	105	102	99	107	104	101	98	101	99	97		99	97	95		97
4	106	101	98	95	105	100	97	95	99	96	94		97	95	93		95
5	104	98	95	92	102	98	94	92	96	93	91		95	92	90		93
6	101	96	92	89	100	95	92	89	94	91	89		93	90	88		92
7	99	93	90	87	98	93	89	87	92	89	86		91	88	86		90
8	97	91	87	85	96	91	87	85	90	87	85		89	86	84		88
9	95	89	85	83	94	89	85	83	88	85	83		87	84	83		87
10	93	87	84	81	92	87	83	81	86	83	81		86	83	81		85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2674325
5°	2251656
10°	1406365
15°	525792
20°	180476
25°	75222
30°	35423
35°	15874
40°	7500
45°	3845
50°	1399
55°	268
60°	307
65°	363
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3845 cd/sqm

TEST NUMBER: P1260285

CATALOG NUMBER: P3AS17R209050DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	850.7	48.3
10°-20°	700.7	39.7
20°-30°	159.2	9.0
30°-40°	40.5	2.3
40°-50°	10.2	0.6
50°-60°	1.3	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1710.6	97.0
0°-40°	1751.1	99.3
0°-60°	1762.6	100.0
0°-90°	1763.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1763.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12196	
5°	10229	851
15°	2316	701
25°	311	159
35°	59	41
45°	12	10
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1260285

CATALOG NUMBER: P3AS17R209050DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	12195.9
1°	12092.5
2°	11787.8
3°	11350.8
4°	10814.5
5°	10229.3
6°	9577.2
7°	8857.6
8°	8018.0
9°	7186.0
10°	6316.1
11°	5390.4
12°	4466.0
13°	3683.0
14°	2934.4
15°	2316.1
16°	1828.0
17°	1442.0
18°	1158.7
19°	942.3
20°	773.4
21°	646.6
22°	539.7
23°	448.7
24°	374.3
25°	310.9
27.5°	203.3
30°	139.9
32.5°	86.2
35°	59.3
37.5°	37.9
40°	26.2
42.5°	17.9
45°	12.4
47.5°	8.3
50°	4.1
52.5°	2.1
55°	0.7
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P1260285

CATALOG NUMBER: P3AS17R209050DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)