

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260970

Luminaire Tested: P3AS24R209050D010 E3CB1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260970
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R209050D010 E3CB1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 5000K CCT AND, 90CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2607.1 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260970

CATALOG NUMBER: P3AS24R209050D010 E3CB1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1260970

CATALOG NUMBER: P3AS24R209050D010 E3CB1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	110	113	112	110	109	108	106	105		104	103	102		101
2	112	109	107	104	110	108	105	103	104	103	101		102	100	99		99
3	109	105	102	100	108	104	101	99	102	99	97		99	98	96		97
4	107	102	99	96	105	101	98	96	99	97	95		97	95	93		96
5	104	99	96	93	103	98	95	93	97	94	92		95	93	91		94
6	102	97	93	91	101	96	93	90	95	92	90		94	91	89		93
7	100	94	91	88	99	94	91	88	93	90	88		92	89	87		91
8	98	92	89	86	97	92	89	86	91	88	86		90	88	86		89
9	96	90	87	85	95	90	87	85	89	86	84		89	86	84		88
10	94	89	85	83	93	88	85	83	88	85	83		87	84	83		86

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4048974
5°	3514365
10°	2171503
15°	754215
20°	231627
25°	81876
30°	30308
35°	12153
40°	6498
45°	2574
50°	1399
55°	1567
60°	1798
65°	1090
70°	1346
75°	1779
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2574 cd/sqm

TEST NUMBER: P1260970

CATALOG NUMBER: P3AS24R209050D010 E3CB1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1325.0	50.8
10°-20°	1051.3	40.3
20°-30°	182.0	7.0
30°-40°	33.1	1.3
40°-50°	7.6	0.3
50°-60°	3.7	0.1
60°-70°	2.3	0.1
70°-80°	1.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2558.4	98.1
0°-40°	2591.5	99.4
0°-60°	2602.8	99.8
0°-90°	2607.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2607.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	18465	
5°	15966	###
15°	3322	1051
25°	338	182
35°	45	33
45°	8	8
55°	4	4
65°	2	2
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1260970

CATALOG NUMBER: P3AS24R209050D010 E3CB1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	18464.8
1°	18376.0
2°	18025.2
3°	17461.9
4°	16801.5
5°	15965.8
6°	15008.3
7°	13894.0
8°	12624.9
9°	11199.0
10°	9752.4
12.5°	6151.5
15°	3322.3
17.5°	1774.7
20°	992.6
22.5°	567.5
25°	338.4
27.5°	206.4
30°	119.7
32.5°	70.2
35°	45.4
37.5°	31.0
40°	22.7
42.5°	14.4
45°	8.3
47.5°	4.1
50°	4.1
52.5°	4.1
55°	4.1
57.5°	4.1
60°	4.1
62.5°	2.1
65°	2.1
67.5°	2.1
70°	2.1
72.5°	2.1
75°	2.1
77.5°	2.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)