

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261003

Luminaire Tested: P3AS24R259050D010 E3D1WH

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1261003  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R259050D010 E3D1WH  
Description: 3in Adjustable LED luminaire with, R25 optic, 5000K CCT AND, 90CRI , E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2789.9 lumens  
Efficiency: N/A  
Efficacy: 96.9 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1261003  
CATALOG NUMBER: P3AS24R259050D010 E3D1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1261003  
 CATALOG NUMBER: P3AS24R259050D010 E3D1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97	97	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	96	96	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92
4	106	101	97	94	104	100	96	94	98	95	92	96	93	91	94	92	90	89	89	89
5	103	97	93	91	101	96	93	90	95	92	90	93	91	89	92	90	88	87	87	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	85	85
7	98	92	88	85	97	91	87	85	90	87	84	89	86	84	88	86	84	83	83	83
8	95	89	85	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81	81	81
9	93	87	83	81	92	86	83	80	86	83	80	85	82	80	84	82	80	79	79	79
10	91	85	81	79	90	84	81	79	84	81	78	83	80	78	83	80	78	77	77	77

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3055567
5°	2830545
10°	2190028
15°	1046022
20°	344873
25°	145387
30°	56338
35°	24360
40°	8101
45°	3752
50°	1365
55°	765
60°	439
65°	519
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3752 cd/sqm



TEST NUMBER: P1261003  
 CATALOG NUMBER: P3AS24R259050D010 E3D1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1130.3	40.5
10°-20°	1285.6	46.1
20°-30°	298.7	10.7
30°-40°	62.7	2.2
40°-50°	10.1	0.4
50°-60°	1.7	0.1
60°-70°	0.9	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2714.6	97.3
0°-40°	2777.3	99.5
0°-60°	2789.1	100.0
0°-90°	2789.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2789.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	13934	
5°	12859	###
15°	4608	1286
25°	601	299
35°	91	63
45°	12	10
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1261003  
CATALOG NUMBER: P3AS24R259050D010 E3D1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	13934.5
1°	13906.2
2°	13761.5
3°	13558.2
4°	13247.7
5°	12859.2
6°	12360.5
7°	11838.5
8°	11252.8
9°	10592.3
10°	9835.6
11°	8958.6
12°	7952.0
13°	6849.4
14°	5696.2
15°	4607.7
16°	3644.7
17°	2839.5
18°	2233.6
19°	1786.5
20°	1477.9
21°	1235.1
22°	1036.9
23°	865.9
24°	724.3
25°	600.9
27.5°	356.1
30°	222.5
32.5°	142.6
35°	91.0
37.5°	54.6
40°	28.3
42.5°	18.2
45°	12.1
47.5°	7.1
50°	4.0
52.5°	2.0
55°	2.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	1.0
70°	0.0
72.5°	0.0



TEST NUMBER: P1261003  
CATALOG NUMBER: P3AS24R259050D010 E3D1WH

**CANDELA DISTRIBUTION (continued):**

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)