

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260328

Luminaire Tested: P3AS17R259050DE010 E3DLP1H

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1260328  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R259050DE010 E3DLP1H  
Description: 3in Adjustable LED luminaire with, R25 optic, 5000K CCT AND, 90CRI , E3DLP1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 901.9 lumens  
Efficiency: N/A  
Efficacy: 42.5 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1260328

CATALOG NUMBER: P3AS17R259050DE010 E3DLP1H

### Luminous Intensity Polar Plot



TEST NUMBER: P1260328

CATALOG NUMBER: P3AS17R259050DE010 E3DLP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 101 |  | 100 | 99  | 98  |  | 97  |
| 2   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 94  | 97  | 94  | 92  |  | 94  | 92  | 90  |  | 92  |
| 3   | 102 | 95  | 90  | 86  | 100 | 94  | 89  | 86  | 91  | 87  | 84  |  | 89  | 86  | 83  |  | 87  |
| 4   | 97  | 89  | 84  | 79  | 95  | 88  | 83  | 79  | 86  | 81  | 78  |  | 84  | 80  | 77  |  | 82  |
| 5   | 92  | 84  | 78  | 74  | 91  | 83  | 77  | 73  | 81  | 76  | 73  |  | 79  | 75  | 72  |  | 78  |
| 6   | 88  | 79  | 73  | 69  | 86  | 78  | 72  | 68  | 77  | 72  | 68  |  | 75  | 71  | 67  |  | 74  |
| 7   | 84  | 74  | 68  | 64  | 82  | 74  | 68  | 64  | 72  | 67  | 64  |  | 71  | 67  | 63  |  | 70  |
| 8   | 80  | 70  | 65  | 60  | 79  | 70  | 64  | 60  | 69  | 64  | 60  |  | 68  | 63  | 60  |  | 67  |
| 9   | 76  | 67  | 61  | 57  | 75  | 66  | 61  | 57  | 65  | 60  | 57  |  | 65  | 60  | 57  |  | 64  |
| 10  | 73  | 64  | 58  | 54  | 72  | 63  | 58  | 54  | 62  | 57  | 54  |  | 62  | 57  | 54  |  | 61  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 327474 |
| 5°  | 314175 |
| 10° | 275234 |
| 15° | 221227 |
| 20° | 169975 |
| 25° | 128620 |
| 30° | 92926  |
| 35° | 61730  |
| 40° | 37442  |
| 45° | 21801  |
| 50° | 13919  |
| 55° | 11278  |
| 60° | 9868   |
| 65° | 8769   |
| 70° | 7181   |
| 75° | 7117   |
| 80° | 5304   |
| 85° | 7045   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21801 cd/sqm

TEST NUMBER: P1260328

CATALOG NUMBER: P3AS17R259050DE010 E3DLP1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 129.9  | 14.4      |
| 10°-20°   | 269.5  | 29.9      |
| 20°-30°   | 243.7  | 27.0      |
| 30°-40°   | 146.4  | 16.2      |
| 40°-50°   | 58.1   | 6.4       |
| 50°-60°   | 26.8   | 3.0       |
| 60°-70°   | 16.4   | 1.8       |
| 70°-80°   | 8.7    | 1.0       |
| 80°-90°   | 2.5    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 643.1  | 71.3      |
| 0°-40°    | 789.5  | 87.5      |
| 0°-60°    | 874.4  | 97.0      |
| 0°-90°    | 901.9  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 901.9  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1493 |      |
| 5°  | 1427 | 130  |
| 15° | 974  | 269  |
| 25° | 532  | 244  |
| 35° | 231  | 146  |
| 45° | 70   | 58   |
| 55° | 30   | 27   |
| 65° | 17   | 16   |
| 75° | 8    | 9    |
| 85° | 3    | 2    |
| 90° | 0    |      |

TEST NUMBER: P1260328

CATALOG NUMBER: P3AS17R259050DE010 E3DLP1H

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1493.4 |
| 1°    | 1493.4 |
| 2°    | 1486.4 |
| 3°    | 1470.9 |
| 4°    | 1451.2 |
| 5°    | 1427.3 |
| 6°    | 1396.4 |
| 7°    | 1361.2 |
| 8°    | 1320.4 |
| 9°    | 1279.7 |
| 10°   | 1236.1 |
| 11°   | 1185.4 |
| 12°   | 1133.4 |
| 13°   | 1081.4 |
| 14°   | 1029.4 |
| 15°   | 974.5  |
| 17.5° | 845.1  |
| 20°   | 728.4  |
| 22.5° | 623.0  |
| 25°   | 531.6  |
| 27.5° | 445.8  |
| 30°   | 367.0  |
| 32.5° | 295.3  |
| 35°   | 230.6  |
| 37.5° | 175.8  |
| 40°   | 130.8  |
| 42.5° | 95.6   |
| 45°   | 70.3   |
| 47.5° | 53.4   |
| 50°   | 40.8   |
| 52.5° | 33.7   |
| 55°   | 29.5   |
| 57.5° | 25.3   |
| 60°   | 22.5   |
| 62.5° | 18.3   |
| 65°   | 16.9   |
| 67.5° | 14.1   |
| 70°   | 11.2   |
| 72.5° | 9.8    |
| 75°   | 8.4    |
| 77.5° | 7.0    |
| 80°   | 4.2    |
| 82.5° | 2.8    |
| 85°   | 2.8    |
| 87.5° | 1.4    |



TEST NUMBER: P1260328  
CATALOG NUMBER: P3AS17R259050DE010 E3DLP1H

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)