

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261004

Luminaire Tested: P3AS24R259050D010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261004
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R259050D010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 5000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2789.9 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261004

CATALOG NUMBER: P3AS24R259050D010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1261004

CATALOG NUMBER: P3AS24R259050D010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	110		113	111	110	108		107	106	105		104	103	102		100	99	99
2	112	108	106	103		110	107	104	102		104	102	100		101	99	98		98	97	96
3	109	104	101	98		107	103	100	97		100	98	96		98	96	94		96	94	93
4	106	101	97	94		104	100	96	94		98	95	92		96	93	91		94	92	90
5	103	97	93	91		101	96	93	90		95	92	90		93	91	89		92	90	88
6	100	94	90	88		99	94	90	87		92	89	87		91	88	86		90	88	86
7	98	92	88	85		97	91	87	85		90	87	84		89	86	84		88	86	84
8	95	89	85	83		94	89	85	83		88	85	82		87	84	82		86	84	82
9	93	87	83	81		92	86	83	80		86	83	80		85	82	80		84	82	80
10	91	85	81	79		90	84	81	79		84	81	78		83	80	78		83	80	78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3055567
5°	2830545
10°	2190028
15°	1046022
20°	344873
25°	145387
30°	56338
35°	24360
40°	8101
45°	3752
50°	1365
55°	765
60°	439
65°	519
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3752 cd/sqm

TEST NUMBER: P1261004

CATALOG NUMBER: P3AS24R259050D010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1130.3	40.5
10°-20°	1285.6	46.1
20°-30°	298.7	10.7
30°-40°	62.7	2.2
40°-50°	10.1	0.4
50°-60°	1.7	0.1
60°-70°	0.9	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2714.6	97.3
0°-40°	2777.3	99.5
0°-60°	2789.1	100.0
0°-90°	2789.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2789.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13934	
5°	12859	###
15°	4608	1286
25°	601	299
35°	91	63
45°	12	10
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1261004

CATALOG NUMBER: P3AS24R259050D010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	13934.5
1°	13906.2
2°	13761.5
3°	13558.2
4°	13247.7
5°	12859.2
6°	12360.5
7°	11838.5
8°	11252.8
9°	10592.3
10°	9835.6
11°	8958.6
12°	7952.0
13°	6849.4
14°	5696.2
15°	4607.7
16°	3644.7
17°	2839.5
18°	2233.6
19°	1786.5
20°	1477.9
21°	1235.1
22°	1036.9
23°	865.9
24°	724.3
25°	600.9
27.5°	356.1
30°	222.5
32.5°	142.6
35°	91.0
37.5°	54.6
40°	28.3
42.5°	18.2
45°	12.1
47.5°	7.1
50°	4.0
52.5°	2.0
55°	2.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	1.0
70°	0.0
72.5°	0.0

TEST NUMBER: P1261004

CATALOG NUMBER: P3AS24R259050D010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)