

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261005

Luminaire Tested: P3AS24R259050D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261005
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R259050D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 5000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1059.0 lumens
Efficiency: N/A
Efficacy: 36.8 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261005
CATALOG NUMBER: P3AS24R259050D010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1261005
 CATALOG NUMBER: P3AS24R259050D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	66	66	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	679310
5°	633787
10°	507717
15°	344633
20°	208525
25°	121943
30°	69454
35°	38200
40°	20267
45°	10668
50°	6209
55°	4626
60°	3991
65°	4203
70°	3911
75°	3389
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10668 cd/sqm



TEST NUMBER: P1261005
 CATALOG NUMBER: P3AS24R259050D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.5	24.1
10°-20°	417.4	39.4
20°-30°	238.5	22.5
30°-40°	94.1	8.9
40°-50°	28.8	2.7
50°-60°	11.4	1.1
60°-70°	7.7	0.7
70°-80°	4.3	0.4
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	911.4	86.1
0°-40°	1005.5	94.9
0°-60°	1045.7	98.7
0°-90°	1059.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1059.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3098	
5°	2879	256
15°	1518	417
25°	504	238
35°	143	94
45°	34	29
55°	12	11
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1261005
CATALOG NUMBER: P3AS24R259050D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3097.9
1°	3091.8
2°	3066.5
3°	3022.0
4°	2960.3
5°	2879.3
6°	2784.2
7°	2676.9
8°	2552.4
9°	2424.9
10°	2280.2
11°	2137.5
12°	1980.6
13°	1825.7
14°	1666.9
15°	1518.1
17.5°	1177.0
20°	893.6
22.5°	671.0
25°	504.0
27.5°	373.4
30°	274.3
32.5°	198.4
35°	142.7
37.5°	101.2
40°	70.8
42.5°	48.6
45°	34.4
47.5°	24.3
50°	18.2
52.5°	14.2
55°	12.1
57.5°	11.1
60°	9.1
62.5°	8.1
65°	8.1
67.5°	7.1
70°	6.1
72.5°	5.1
75°	4.0
77.5°	3.0
80°	2.0
82.5°	2.0
85°	1.0
87.5°	1.0



TEST NUMBER: P1261005
CATALOG NUMBER: P3AS24R259050D010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)