

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260345

Luminaire Tested: P3AS17R309050DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260345
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R309050DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R30 optic, 5000K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1776.0 lumens
Efficiency: N/A
Efficacy: 83.8 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260345
CATALOG NUMBER: P3AS17R309050DE010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1260345
 CATALOG NUMBER: P3AS17R309050DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	90	89	88
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	88	86	85
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	85	84	82
6	99	92	88	85	97	92	88	85	90	87	85	89	86	84	88	85	83	82	81	80
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	80	79	78
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	77	76
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	82	79	77	76	75	74
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	80	77	75	74	73	72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1413045
5°	1394603
10°	1217635
15°	773943
20°	306627
25°	102417
30°	47653
35°	21603
40°	8301
45°	4062
50°	1160
55°	535
60°	307
65°	363
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4062 cd/sqm



TEST NUMBER: P1260345
 CATALOG NUMBER: P3AS17R309050DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	579.3	32.6
10°-20°	898.3	50.6
20°-30°	231.6	13.0
30°-40°	54.4	3.1
40°-50°	10.6	0.6
50°-60°	1.2	0.1
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1709.2	96.2
0°-40°	1763.6	99.3
0°-60°	1775.4	100.0
0°-90°	1776.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1776.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6444	
5°	6336	579
15°	3409	898
25°	423	232
35°	81	54
45°	13	11
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1260345
CATALOG NUMBER: P3AS17R309050DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	6444.0
1°	6439.2
2°	6424.0
3°	6406.7
4°	6381.2
5°	6335.7
6°	6262.0
7°	6139.3
8°	5971.7
9°	5753.2
10°	5468.5
11°	5130.0
12°	4760.4
13°	4335.1
14°	3889.7
15°	3409.2
16°	2938.3
17°	2484.7
18°	2049.6
19°	1650.5
20°	1314.0
21°	1034.1
22°	813.5
23°	643.9
24°	515.7
25°	423.3
26°	353.0
27°	299.9
28°	259.2
29°	222.0
30°	188.2
32.5°	118.6
35°	80.7
37.5°	50.3
40°	29.0
42.5°	19.3
45°	13.1
47.5°	7.6
50°	3.4
52.5°	1.4
55°	1.4
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7



TEST NUMBER: P1260345
CATALOG NUMBER: P3AS17R309050DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)