

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261027

Luminaire Tested: P3AS24R309050D010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261027
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R309050D010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R30 optic, 5000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2627.0 lumens
Efficiency: N/A
Efficacy: 91.2 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261027
CATALOG NUMBER: P3AS24R309050D010 E3CB1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1261027
 CATALOG NUMBER: P3AS24R309050D010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	876.5	33.4
10°-20°	1366.0	52.0
20°-30°	317.2	12.1
30°-40°	49.1	1.9
40°-50°	8.4	0.3
50°-60°	3.9	0.1
60°-70°	3.3	0.1
70°-80°	2.2	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2559.7	97.4
0°-40°	2608.9	99.3
0°-60°	2621.2	99.8
0°-90°	2627.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2627.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9756	
5°	9535	877
15°	5185	1366
25°	547	317
35°	60	49
45°	8	8
55°	4	4
65°	4	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1261027
CATALOG NUMBER: P3AS24R309050D010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	9755.8
1°	9749.6
2°	9722.8
3°	9677.4
4°	9619.6
5°	9535.0
6°	9429.8
7°	9273.0
8°	9058.4
9°	8742.7
10°	8344.4
11°	7830.7
12°	7250.8
13°	6607.1
14°	5899.3
15°	5185.4
17.5°	3392.3
20°	1914.8
22.5°	978.1
25°	546.8
27.5°	336.3
30°	206.3
32.5°	111.4
35°	59.8
37.5°	39.2
40°	24.8
42.5°	14.4
45°	8.3
47.5°	6.2
50°	6.2
52.5°	4.1
55°	4.1
57.5°	4.1
60°	4.1
62.5°	4.1
65°	4.1
67.5°	2.1
70°	2.1
72.5°	2.1
75°	2.1
77.5°	2.1
80°	2.1
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1261027
CATALOG NUMBER: P3AS24R309050D010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)