

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260348

Luminaire Tested: P3AS17R309050DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260348
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R309050DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R30 optic, 5000K CCT AND, 90CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1489.0 lumens
Efficiency: N/A
Efficacy: 70.2 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260348
CATALOG NUMBER: P3AS17R309050DE010 E3DL1H

Luminous Intensity Polar Plot





TEST NUMBER: P1260348
 CATALOG NUMBER: P3AS17R309050DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	93	92	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	91	89	87	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	88	85	83	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	85	82	79	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	81	78	76	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	79	75	73	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	79	75	73	71	76	72	70	71
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	73	70	67	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63	71	67	65	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	868878
5°	826984
10°	695623
15°	501660
20°	311177
25°	176962
30°	98294
35°	53458
40°	28196
45°	15257
50°	8153
55°	5390
60°	4956
65°	5085
70°	4488
75°	3558
80°	3536
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15257 cd/sqm



TEST NUMBER: P1260348
 CATALOG NUMBER: P3AS17R309050DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	338.3	22.7
10°-20°	601.4	40.4
20°-30°	347.5	23.3
30°-40°	131.9	8.9
40°-50°	40.5	2.7
50°-60°	13.7	0.9
60°-70°	9.2	0.6
70°-80°	5.0	0.3
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1287.2	86.5
0°-40°	1419.1	95.3
0°-60°	1473.3	98.9
0°-90°	1489.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1489.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3962	
5°	3757	338
15°	2210	601
25°	731	348
35°	200	132
45°	49	40
55°	14	14
65°	10	9
75°	4	5
85°	1	2
90°	0	



TEST NUMBER: P1260348
CATALOG NUMBER: P3AS17R309050DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	3962.4
1°	3959.6
2°	3935.7
3°	3890.7
4°	3834.4
5°	3757.0
6°	3658.6
7°	3548.9
8°	3426.5
9°	3280.2
10°	3124.1
11°	2955.3
12°	2776.6
13°	2589.6
14°	2399.7
15°	2209.8
17.5°	1742.8
20°	1333.5
22.5°	988.8
25°	731.4
27.5°	531.7
30°	388.2
32.5°	279.9
35°	199.7
37.5°	139.3
40°	98.5
42.5°	68.9
45°	49.2
47.5°	33.8
50°	23.9
52.5°	16.9
55°	14.1
57.5°	12.7
60°	11.3
62.5°	9.8
65°	9.8
67.5°	8.4
70°	7.0
72.5°	5.6
75°	4.2
77.5°	4.2
80°	2.8
82.5°	2.8
85°	1.4
87.5°	0.0



TEST NUMBER: P1260348
CATALOG NUMBER: P3AS17R309050DE010 E3DL1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)