

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260435

Luminaire Tested: P3AS17R459050DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260435
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R459050DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R45 optic, 5000K CCT AND, 90CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1572.0 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260435
CATALOG NUMBER: P3AS17R459050DE010 E3DL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1260435

CATALOG NUMBER: P3AS17R459050DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88	88	88	88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83	83	83	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78	78	78	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74	74	74	74
6	90	82	77	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70	70	70	70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66	66	66	66
8	83	74	68	65	82	73	68	65	72	68	64	71	67	64	70	67	64	62	62	62	62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59	59	59	59
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57	57	57	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	590347
5°	576512
10°	529961
15°	449038
20°	348397
25°	243546
30°	153416
35°	90319
40°	51096
45°	24840
50°	8631
55°	6996
60°	6798
65°	6590
70°	6283
75°	5931
80°	5304
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24840 cd/sqm



TEST NUMBER: P1260435
 CATALOG NUMBER: P3AS17R459050DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	242.4	15.4
10°-20°	543.2	34.6
20°-30°	461.2	29.3
30°-40°	220.0	14.0
40°-50°	66.3	4.2
50°-60°	16.8	1.1
60°-70°	12.5	0.8
70°-80°	7.4	0.5
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1246.9	79.3
0°-40°	1466.9	93.3
0°-60°	1550.0	98.6
0°-90°	1572.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1572.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2692	
5°	2619	242
15°	1978	543
25°	1007	461
35°	337	220
45°	80	66
55°	18	17
65°	13	13
75°	7	7
85°	1	2
90°	0	



TEST NUMBER: P1260435
CATALOG NUMBER: P3AS17R459050DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2692.2
2.5°	2675.3
5°	2619.1
7.5°	2522.1
10°	2380.1
12.5°	2191.7
15°	1978.0
17.5°	1740.4
20°	1493.0
22.5°	1241.3
25°	1006.6
27.5°	792.9
30°	605.9
32.5°	455.5
35°	337.4
37.5°	248.8
40°	178.5
42.5°	123.7
45°	80.1
47.5°	45.0
50°	25.3
52.5°	19.7
55°	18.3
57.5°	16.9
60°	15.5
62.5°	14.1
65°	12.7
67.5°	11.2
70°	9.8
72.5°	8.4
75°	7.0
77.5°	5.6
80°	4.2
82.5°	2.8
85°	1.4
87.5°	1.4
90°	0.0

(END OF REPORT)