

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261114

Luminaire Tested: P3AS24R409050D010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261114
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R409050D010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 5000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1517.0 lumens
Efficiency: N/A
Efficacy: 52.7 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261114

CATALOG NUMBER: P3AS24R409050D010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1261114

CATALOG NUMBER: P3AS24R409050D010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	472353
5°	462799
10°	430898
15°	375553
20°	302660
25°	226876
30°	159493
35°	104480
40°	63261
45°	37802
50°	22549
55°	18159
60°	16314
65°	13906
70°	13271
75°	10506
80°	10481
85°	10315

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 37802 cd/sqm

TEST NUMBER: P1261114

CATALOG NUMBER: P3AS24R409050D010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.2	12.9
10°-20°	455.7	30.0
20°-30°	429.4	28.3
30°-40°	248.3	16.4
40°-50°	98.9	6.5
50°-60°	43.8	2.9
60°-70°	27.1	1.8
70°-80°	14.2	0.9
80°-90°	4.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1080.3	71.2
0°-40°	1328.6	87.6
0°-60°	1471.3	97.0
0°-90°	1517.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1517.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2154	
5°	2102	195
15°	1654	456
25°	938	429
35°	390	248
45°	122	99
55°	48	44
65°	27	27
75°	12	14
85°	4	5
90°	0	

TEST NUMBER: P1261114

CATALOG NUMBER: P3AS24R409050D010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2154.1
2.5°	2141.7
5°	2102.5
7.5°	2030.2
10°	1935.2
12.5°	1807.2
15°	1654.3
17.5°	1482.9
20°	1297.0
22.5°	1111.1
25°	937.7
27.5°	776.6
30°	629.9
32.5°	501.9
35°	390.3
37.5°	295.3
40°	221.0
42.5°	165.2
45°	121.9
47.5°	88.8
50°	66.1
52.5°	53.7
55°	47.5
57.5°	43.4
60°	37.2
62.5°	31.0
65°	26.8
67.5°	22.7
70°	20.7
72.5°	16.5
75°	12.4
77.5°	10.3
80°	8.3
82.5°	6.2
85°	4.1
87.5°	2.1
90°	0.0

(END OF REPORT)