

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261139

Luminaire Tested: P3AS24R459050D010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261139
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R459050D010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 5000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1489.0 lumens
Efficiency: N/A
Efficacy: 51.7 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261139

CATALOG NUMBER: P3AS24R459050D010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1261139

CATALOG NUMBER: P3AS24R459050D010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	443517
5°	433391
10°	399814
15°	347652
20°	285601
25°	222206
30°	164101
35°	115456
40°	72078
45°	39043
50°	21117
55°	18159
60°	16271
65°	13906
70°	11925
75°	12200
80°	10481
85°	10315

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 39043 cd/sqm

TEST NUMBER: P1261139

CATALOG NUMBER: P3AS24R459050D010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.4	12.2
10°-20°	423.4	28.4
20°-30°	420.3	28.2
30°-40°	270.7	18.2
40°-50°	104.3	7.0
50°-60°	42.4	2.8
60°-70°	26.8	1.8
70°-80°	14.4	1.0
80°-90°	4.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1026.0	68.9
0°-40°	1296.7	87.1
0°-60°	1443.3	96.9
0°-90°	1489.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1489.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2023	
5°	1969	182
15°	1531	423
25°	918	420
35°	431	271
45°	126	104
55°	48	42
65°	27	27
75°	14	14
85°	4	5
90°	0	

TEST NUMBER: P1261139

CATALOG NUMBER: P3AS24R459050D010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2022.6
2.5°	2012.3
5°	1968.9
7.5°	1894.6
10°	1795.6
12.5°	1671.7
15°	1531.4
17.5°	1378.7
20°	1223.9
22.5°	1067.0
25°	918.4
27.5°	778.1
30°	648.1
32.5°	534.5
35°	431.3
37.5°	338.5
40°	251.8
42.5°	181.6
45°	125.9
47.5°	84.6
50°	61.9
52.5°	51.6
55°	47.5
57.5°	41.3
60°	37.1
62.5°	31.0
65°	26.8
67.5°	22.7
70°	18.6
72.5°	16.5
75°	14.4
77.5°	10.3
80°	8.3
82.5°	6.2
85°	4.1
87.5°	2.1
90°	0.0

(END OF REPORT)