

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261173

Luminaire Tested: P3AS24R559050D010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261173
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R559050D010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R55 optic, 5000K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2747.0 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261173

CATALOG NUMBER: P3AS24R559050D010 E3CD1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1261173

CATALOG NUMBER: P3AS24R559050D010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	98	107	103	99	96	100	97	94		97	94	92		94	92	90	89
3	104	98	94	90	102	97	93	89	94	91	88		92	89	86		90	87	85	84
4	99	92	87	84	98	91	87	83	89	85	82		87	84	81		85	83	80	79
5	95	87	82	78	93	86	81	78	85	80	77		83	79	76		82	78	76	74
6	91	83	77	73	89	82	77	73	80	76	72		79	75	72		78	74	72	70
7	87	78	73	69	85	78	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	61	78	70	65	61	69	64	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	761891
5°	754808
10°	785134
15°	774238
20°	713969
25°	580921
30°	352839
35°	122121
40°	34865
45°	16653
50°	7027
55°	3173
60°	3640
65°	3217
70°	2629
75°	3474
80°	2652
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16653 cd/sqm

TEST NUMBER: P1261173

CATALOG NUMBER: P3AS24R559050D010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	331.5	12.1
10°-20°	947.9	34.5
20°-30°	1056.7	38.5
30°-40°	345.7	12.6
40°-50°	45.6	1.7
50°-60°	9.7	0.4
60°-70°	5.6	0.2
70°-80°	3.5	0.1
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2336.1	85.0
0°-40°	2681.8	97.6
0°-60°	2737.0	99.6
0°-90°	2747.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2747.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3474	
5°	3429	332
15°	3410	948
25°	2401	1057
35°	456	346
45°	54	46
55°	8	10
65°	6	6
75°	4	4
85°	0	1
90°	0	

TEST NUMBER: P1261173

CATALOG NUMBER: P3AS24R559050D010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	3474.5
2.5°	3449.7
5°	3429.1
7.5°	3478.6
10°	3526.1
12.5°	3501.4
15°	3410.5
17.5°	3266.0
20°	3059.6
22.5°	2774.7
25°	2401.0
27.5°	1926.2
30°	1393.5
32.5°	854.7
35°	456.2
37.5°	231.2
40°	121.8
42.5°	78.5
45°	53.7
47.5°	37.2
50°	20.6
52.5°	12.4
55°	8.3
57.5°	8.3
60°	8.3
62.5°	6.2
65°	6.2
67.5°	4.1
70°	4.1
72.5°	4.1
75°	4.1
77.5°	2.1
80°	2.1
82.5°	2.1
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)