

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260477

Luminaire Tested: P3AS17R509050DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260477
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R509050DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R50 optic, 5000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1582.0 lumens
Efficiency: N/A
Efficacy: 74.6 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260477

CATALOG NUMBER: P3AS17R509050DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1260477

CATALOG NUMBER: P3AS17R509050DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	503688
5°	493527
10°	462272
15°	413828
20°	348257
25°	265781
30°	172735
35°	102419
40°	59197
45°	29646
50°	11053
55°	8602
60°	8026
65°	7316
70°	7245
75°	7117
80°	7072
85°	7045

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 29646 cd/sqm

TEST NUMBER: P1260477

CATALOG NUMBER: P3AS17R509050DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.6	13.2
10°-20°	504.1	31.9
20°-30°	494.6	31.3
30°-40°	249.2	15.8
40°-50°	78.7	5.0
50°-60°	20.4	1.3
60°-70°	14.5	0.9
70°-80°	8.9	0.6
80°-90°	3.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1207.3	76.3
0°-40°	1456.4	92.1
0°-60°	1555.6	98.3
0°-90°	1582.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1582.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2297	
5°	2242	209
15°	1823	504
25°	1098	495
35°	383	249
45°	96	79
55°	22	20
65°	14	14
75°	8	9
85°	3	3
90°	0	

TEST NUMBER: P1260477

CATALOG NUMBER: P3AS17R509050DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2297.0
2.5°	2282.9
5°	2242.1
7.5°	2169.0
10°	2076.1
12.5°	1956.6
15°	1822.9
17.5°	1668.2
20°	1492.4
22.5°	1302.5
25°	1098.5
27.5°	881.9
30°	682.2
32.5°	513.4
35°	382.6
37.5°	282.7
40°	206.8
42.5°	146.3
45°	95.6
47.5°	54.9
50°	32.4
52.5°	23.9
55°	22.5
57.5°	19.7
60°	18.3
62.5°	16.9
65°	14.1
67.5°	12.7
70°	11.3
72.5°	9.8
75°	8.4
77.5°	7.0
80°	5.6
82.5°	4.2
85°	2.8
87.5°	1.4
90°	0.0

(END OF REPORT)